



Product: [3115A](#)

Type JX Thermocouple, 2 Pr #20+22 Sol, PVC Ins Wht, Red, IS/OS, Blk PVC Jkt, 300V PLTC-ER ITC-ER CMG

[Request Sample](#)

Product Description

Type JX Thermocouple, 2 Pair 20+22AWG (Solid) Iron+Constantan, PVC Insulation Wht, Red Color Code, Individual & Overall Beldfoil® Shield, Black PVC Outer Jacket, PLTC-ER ITC-ER CMG AWM 2464 SUN RES DIR BUR

Technical Specifications

Construction Details

Conductor

Element	Number of Element	Size	Stranding	Material
Pair(s)	2	20 AWG	Solid	Iron & Constantan
Comm	1	22 AWG	7x30	BC - Bare Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Pair(s)	PVC - Polyvinyl Chloride	0.021 in (0.53 mm)	0.074 in (1.9 mm)	Red and White and Numbered
Comm	PVC - Polyvinyl Chloride	0.019 in (0.48 mm)	0.067 in (1.7 mm)	Orange

Inner Shield

Element	Shield Type	Material	Coverage	Drainwire Type
Pair(s)	Tape	Bi-Laminate (Alum+Poly)	100%	20 AWG (7x28) TC

Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	22 AWG (7x30) TC

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.042 in (1.1 mm)	0.378 in

Overall Cable Diameter (Nominal): 0.328 in

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Inner Shield DCR	Max. Current
Iron	69 Ohm/1000ft	8.7 Ohm/1000ft (29 Ohm/km)	
Constantan	293 Ohm/1000ft (961 Ohm/km)		
Comm	17.2 Ohm/1000ft (56.4 Ohm/km)		5 Amps per Conductor at 25°C

Voltage

UL Voltage Rating
300 V

Mechanical Characteristics

Temperature

UL Temperature	Operating

UL: 105°C, AWM 2464: 80°C -20°C to +105°C

Bend Radius

Stationary Min.	Installation Min.
3.28 in (83.3 mm)	3.28 in

Max. Pull Tension:	445 lbs (202 kg)
Bulk Cable Weight:	68 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor, Outdoor, Sunlight Resistance
Flammability / Reaction to Fire:	UL1685 FT4 Loading, FT4, IEEE 1202 FT4
NEC / UL Compliance:	Article 725, Article 727, Article 800, CMG, ITC, PLTC
AWM Compliance:	AWM 2464
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Other Standard Compliance(s):	ISA MC 96.1-1982 Type JX

Product Notes

Notes:	Iron & Constantan = ""Constantan is a Hoskins Manufacturing Company trademark.""
--------	--

History

Update and Revision:	Revision Number: 0.421 Revision Date: 11-09-2022
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC
3115A 0105000	Black	Reel	5,000 ft	612825141952

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.