



Part Number: 3120A

DeviceBus® for InterBus®-S, 3 Pr #24 Str TC, PO Ins, OS+TC Brd, PUR Jkt, AWM 20233

[🛒 Request Sample](#)

Product Description

DeviceBus® for InterBus®-S, 3 Pair 24AWG (7x32) Tinned Copper, PO Insulation, Overall Beldfoil®+Tinned Copper Braid(90%) Shield, PUR Outer Jacket, AWM 20233

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
24	7x32	TC - Tinned Copper	3

Conductor Count:

Insulation

Material	Nominal Wall Thickness
PE - Polyethylene	0.016 in

Color Chart

Number	Color
1	White & Brown
2	Pink & Gray
3	Yellow & Green

Outer Shield Material

Type	Layer	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG
Tape	1	Aluminum/Polyester	Beldfoil®	100 %	TC - Tinned Copper	24
Braid	2	TC - Tinned Copper		90 %		

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
PUR - Polyurethane	0.277 in	0.035 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR
26 Ohm/1000ft	2.7 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Shield
15.4 pF/ft

Impedance

Nominal Characteristic Impedance
100 Ohm

Delay

Nominal Velocity of Propagation (VP) [%]
66 %

Current

Max. Recommended Current [A]
2.7 Amps per conductor @ 25°C

Voltage

UL Voltage Rating
300 V RMS

Temperature Range

UL Temp Rating:	80°C
Operating Temp Range:	-40°C To +80°C

Mechanical Characteristics

Oil Resistance:	Yes
Bulk Cable Weight:	54 lbs/1000ft
Max Recommended Pulling Tension:	33 lbs
Min Bend Radius/Minor Axis:	3 in

Standards

UL AWM Style:	20233
CPR Euroclass:	Eca

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Sunlight Resistance:	Yes
------------------------------------	-----

Flammability, LSOH, Toxicity Testing

ISO/IEC Flammability:	IEC 60332-1-2
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	UPC	Length	Footnote
3120A G7W1000	Green, Matte	612825141983	1,000 ft	C
3120A G7W500	Green, Matte	612825141990	500 ft	C
3120A G7W5000	Green, Matte	612825142003	5,000 ft	C

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

History

Update and Revision:	Revision Number: 0.267 Revision Date: 08-22-2019
----------------------	--

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.