



Product: [3124A](#)

DeviceBus® for Square D/Seriplex®, 2 Pr #18+22 Str TC, FPE Ins, OS, PVC Jkt, CM

[Request Sample](#)

Product Description

DeviceBus® for Square D/Seriplex®, 2 Pair 18+22AWG (16x30+7x30) Tinned Copper, FPE Insulation, Overall Beldfoil® Shield, PVC Outer Jacket, CM

Technical Specifications

Product Overview

Suitable Applications:	harsh environment, IIoT, factory or process automation, video, audio, data communication, etc.
------------------------	--

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Power Pair(s)	1	18 AWG	16x30	TC - Tinned Copper
Data Pair(s)	1	22 AWG	7x30	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Color Code	Notes
Power Pair(s)	PE - Polyethylene (Foam)	0.026 in (0.66 mm)	Black & Red	HDPE
Data Pair(s)	PE - Polyethylene (Foam)	0.0315 in (0.800 mm)	White & Green	HDPE

Outer Shield

Shield Type	Material	Coverage	Drainwire Type	Notes
Tape	Bi-Laminate (Alum+Poly)	100%	22 AWG (7x30) TC	Foam PP tape under foil tape

Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.039 in (0.99 mm)	0.308 in (7.82 mm)	Yes

Overall Cable Diameter (Nominal): 0.308 in (7.82 mm)

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Shield	Nom. Characteristic Impedance	Nom. Velocity of Prop.
Power Pair(s)	6.8 Ohm/1000ft (22 Ohm/km)	20 pF/ft		
Data Pair(s)	18.1 Ohm/1000ft (59.4 Ohm/km)	16 pF/ft	120 Ohm	78%

Nom. Outer Shield DCR: 10.7 Ohm/1000ft (35.1 Ohm/km)

Voltage

UL Voltage Rating
300 V (CM), 600 V (UL AWM 20201)

Mechanical Characteristics

Temperature

UL Temperature	Operating
75°C	-20°C to +75°C

Bend Radius

Stationary Min.	Installation Min.
3.75 in (95.3 mm)	3.75 in

Max. Pull Tension:	60 lbs (27 kg)
Bulk Cable Weight:	39.3 lbs/1000ft (58.5 kg/km)

Standards and Compliance

Environmental Suitability:	Indoor
Flammability / Reaction to Fire:	UL1685 UL Loading
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 725, Article 800, CL2, CM
AWM Compliance:	AWM 20201
CEC / C(UL) Compliance:	CM
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.457 Revision Date: 02-03-2025
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
3124A 0031000	Orange	Reel	1,000 ft	612825142010	C

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.