



**Product:** [33316](#)

Lead Wire, #16 Str TC, Silicone Ins, AWM 3212

[Request Sample](#)

**Product Description**

Low Temp Rubber Lead Wire, 16AWG (26x30) Tinned Copper, Silicone Insulation, AWM 3212 CSA TYPE AWM 600V 150C

**Technical Specifications**

**Product Overview**

Suitable Applications:	Class 155(F) or Class 180(H) motor lead systems , high temperature applications, internal wiring of lighting fixtures and appliances
------------------------	--

**Physical Characteristics (Overall)**

**Conductor**

AWG	Stranding	Material	No. of Conductors
16	26x30	TC - Tinned Copper	1

Conductor Count: 1

**Insulation**

Material	Nominal Wall Thickness
Silicone Rubber	0.048 in

**Electrical Characteristics**

**Voltage**

UL Voltage Rating
600 V RMS

**Temperature Range**

UL Temp Rating:	150°C
-----------------	-------

**Mechanical Characteristics**

Recommended Max Baking Cycles:	24 Hours @ 410°F (210°C)
Bulk Cable Weight:	9.5 lbs/1000ft
Min Bend Radius/Minor Axis:	0.62 in

**Standards**

UL AWM Style Compliance:	UL AWM Style 3212
CSA Rating:	600 V, 150°C
CSA AWM Compliance:	CSA AWM I B
CSA Type:	AWM

**Applicable Environmental and Other Programs**

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes

EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
CA Prop 65:	Yes
MII Order #39 (China RoHS):	Yes

## Flammability, LSOH, Toxicity Testing

CSA Flammability:	FT2
UL voltage rating:	600 V RMS

## Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

## Part Number

### Variants

Item #	Color	Putup Type	Length	UPC
33316 010500	Black	Reel	500 ft	612825143468
33316 009500	White	Reel	500 ft	612825143451

Footnote:	F - MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 50'.
-----------	--

## Product Notes

Notes:	Recommended Maximum Baking Cycles: 24 hours @ 410°F (210°C)
--------	---

## History

Update and Revision:	Revision Number: 0.295 Revision Date: 02-16-2021
----------------------	--

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.