



Product: [35414](#)

Lead Wire, #14 Str TC, XLPO Ins, AWM 3436 CSA TYPE CL1251 AND AWM

Request Sample

### Product Description

Rubber Lead Wire, 14AWG (41x30) Tinned Copper, XLPO Insulation, AWM 3436 CSA TYPE CL1251 AND AWM 600V 150C

### Technical Specifications

#### Product Overview

Suitable Applications:	high temperature, internal wiring of appliances and electronic equipments
------------------------	---

#### Physical Characteristics (Overall)

**Conductor**

AWG	Stranding	Material	No. of Conductors
14	41x30	TC - Tinned Copper	1

Conductor Count: 1

**Insulation**

Material	Nominal Diameter	Nominal Wall Thickness
XLPE, XLPO, XLPE (Thermoset)	0.138 in	0.032 in

#### Electrical Characteristics

**Voltage**

UL Voltage Rating
600 V

#### Temperature Range

UL Temp Rating:	150°C (125°C Flexing)
-----------------	-----------------------

#### Standards

UL AWM Style Compliance:	AWM 3436, AWM 3321
CSA Rating:	600 V, 125°C, 150°C
CSA AWM Compliance:	CSA AWM I A
CSA Type:	CL1251, AWM
Military Compliance:	N/A

#### Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
MII Order #39 (China RoHS):	Yes

#### Flammability, LS0H, Toxicity Testing

CSA Flammability:	FT2
UL voltage rating:	600 V RMS

## Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

## Related Part Numbers

### Variants

Item #	Color	Put-Up Type	Length	UPC
35414 010500	Black	Reel	500 ft	612825144847

Footnote: U - TOPCOAT ADDERS ON STOCK SOLID COLORS. MINIMUM ORDER 10,000' PER COLOR COMBINATION. (SEE TOPCOAT ADDER TABLE)

## History

Update and Revision:	Revision Number: 0.351 Revision Date: 02-03-2025
----------------------	--

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.