



**Product:** [3P0.5HH](#)

MachFlex™ LiHH (TP), 3 Pr 0.5mm<sup>2</sup> Str BC, PE Ins, LSZH Jkt

## Product Description

MachFlex™ LiHH (TP), 3 Pair 0.5mm<sup>2</sup> Stranded Bare Copper, Polyethylene Insulation, LSZH Jacket

## Technical Specifications

### Product Overview

Suitable Applications:	Applicable for occasional flexing or fixed installation connecting precision control sensors, pressure gauge, temperature controllers, control panels, vibration monitoring systems, intelligent security controllers, production machinery and many more in signal transmission accuracy required fields and confined space.
------------------------	---

### Construction Details

#### Conductor

Element	Size	Stranding	Material
Pair(s)	0.5 mm <sup>2</sup>	Stranded	BC - Bare Copper

#### Insulation

Material	Color Code
PE - Polyethylene	1. White & Brown, 2. Green & Yellow, 3. Grey & Pink

#### Outer Jacket

Material
LSZH - Low Smoke Zero Halogen (Flame Retardant)

Overall Cable Diameter (Nominal):	6.8 mm (0.27 in)
-----------------------------------	------------------

### Electrical Characteristics

#### Voltage

Voltage Rating
500 V (Max. Operating Voltage)

### Mechanical Characteristics

#### Temperature

Operating	Installation
-5°C to +70°C (Occasional movement)	-40°C to +80°C (Fixed installation)

#### Bend Radius

Stationary Min.	Installation Min.
102 mm (4.02 in)	40.8 mm (1.61 in)

Bulk Cable Weight:	53 kg/km (36 lbs/1000ft)
--------------------	--------------------------

### Standards and Compliance

Environmental Suitability:	UV Resistance
Flammability / Reaction to Fire:	IEC 60332-1-2, DIN VDE 0482-332-1-2, DIN EN 60332-1-2
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2)

Other Standard Compliance(s):	VDE 0812
-------------------------------	----------

## Product Notes

Notes:	Smoke/Halogen Properties : IEC 61034-2, IEC 60754-1, IEC 60754-2
--------	--

## History

Update and Revision:	Revision Number: 0.21 Revision Date: 07-26-2024
----------------------	---

## Part Numbers

### Variants

Item #	Color	Length
3P0.5HH 010100M	Black	100 m
3P0.5HH 010200M	Black	200 m
3P0.5HH 010300M	Black	300 m
3P0.5HH 006100M	Blue	100 m
3P0.5HH 006200M	Blue	200 m
3P0.5HH 006300M	Blue	300 m
3P0.5HH F2V100M	Gray, RAL 7032	100 m
3P0.5HH F2V200M	Gray, RAL 7032	200 m
3P0.5HH F2V300M	Gray, RAL 7032	300 m

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.