



Part Number: 3612

CAT6+ Horizontal, 4pr, UTP, PVC Jkt, CMR

Product Description

CAT6+ (400MHz), 4-Pair, U/UTP-unshielded, Riser-CMR, Premise Horizontal cable, 23 AWG solid bare copper conductors, polyolefin insulation, patented X-spline, ripcord, PVC jacket

Technical Specifications

Product Overview

Environmental Space:	Riser
Suitable Applications:	Premise Horizontal Cable, Gigabit Ethernet, 100BaseTX, 100BaseVG ANYLAN, 155ATM, 622ATM, NTSC/PAL Component or Composite Video, AES/EBU Digital Audio, AES51, RS-422, Noisy Environments

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
23	Solid	BC - Bare Copper	4

Conductor Count:	8
Total Number of Pairs:	4
Conductor Size:	23 AWG

Insulation

Material	
PO - Polyolefin	
Bonded-Pair:	N/A

Color Chart

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness	Ripcord	Separator Material
PVC - Polyvinyl Chloride	0.231 in	0.017 in	Yes	Patented X-Spline Center Member

Electrical Characteristics

Conductor DCR

Max. Conductor DCR	Max. DCR Unbalance
77 Ohm/km	3 %

Capacitance

Max. Capacitance Unbalance	Nom. Mutual Capacitance
330 pF/100m	15.5 pF/ft

Delay

Frequency [MHz]	Max. Delay	Max. Delay Skew	Nominal Velocity of Propagation (VP) [%]	Typical Delay Skew
100 MHz	537.6 ns/100m	35 ns/100m	70 %	35 ns/100m

High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted)	Min. TCL [dB]	Min. ELTCTL [dB]
0.772 MHz	1.8 dB/100m	81.0 dB	81.0 dB	79.2 dB	79.2 dB	75.0 dB	73.0 dB			40.0 dB	37.2 dB
1 MHz	2.0 dB/100m	79.3 dB	79.3 dB	77.3 dB	77.3 dB	72.8 dB	70.8 dB	20.0 dB	100 ± 15 Ohm	40.0 dB	35.0 dB
4 MHz	3.7 dB/100m	70.3 dB	70.3 dB	66.6 dB	66.6 dB	60.8 dB	58.8 dB	23.0 dB	100 ± 15 Ohm	40.0 dB	23.0 dB
8 MHz	5.2 dB/100m	65.8 dB	65.8 dB	60.6 dB	60.6 dB	54.7 dB	52.7 dB	24.5 dB	100 ± 15 Ohm	40.0 dB	16.9 dB
10 MHz	5.8 dB/100m	64.3 dB	64.3 dB	58.5 dB	58.5 dB	52.8 dB	50.8 dB	25.0 dB	100 ± 15 Ohm	40.0 dB	15.0 dB
16 MHz	7.4 dB/100m	61.2 dB	61.2 dB	53.9 dB	53.9 dB	48.7 dB	46.7 dB	25.0 dB	100 ± 15 Ohm	38.0 dB	10.9 dB
20 MHz	8.3 dB/100m	59.8 dB	59.8 dB	51.5 dB	51.5 dB	46.8 dB	44.8 dB	25.0 dB	100 ± 15 Ohm	37.0 dB	9.0 dB
25 MHz	9.3 dB/100m	58.3 dB	58.3 dB	49.1 dB	49.1 dB	44.8 dB	42.8 dB	24.3 dB	100 ± 15 Ohm	36.0 dB	7.0 dB
31.25 MHz	10.4 dB/100m	56.9 dB	56.9 dB	46.5 dB	46.5 dB	42.9 dB	40.9 dB	23.6 dB	100 ± 15 Ohm	35.1 dB	
62.5 MHz	15.0 dB/100m	52.4 dB	52.4 dB	37.4 dB	37.4 dB	36.9 dB	34.9 dB	21.5 dB	100 ± 15 Ohm	32.0 dB	
100 MHz	19.3 dB/100m	49.3 dB	49.3 dB	30.0 dB	30.0 dB	32.8 dB	30.8 dB	20.8 dB	100 ± 15 Ohm	30.0 dB	
155 MHz	24.6 dB/100m	46.4 dB	46.4 dB	21.8 dB	21.8 dB	28.9 dB	26.9 dB	19.5 dB	100 ± 22 Ohm	28.1 dB	
200 MHz	28.3 dB/100m	44.8 dB	44.8 dB	16.5 dB	16.5 dB	26.8 dB	24.8 dB	18.7 dB	100 ± 22 Ohm	27.0 dB	
250 MHz	32.1 dB/100m	43.3 dB	43.3 dB	11.2 dB	11.2 dB	24.8 dB	22.8 dB	18.0 dB	100 ± 32 Ohm	26.0 dB	
300 MHz	35.6 dB/100m	42.1 dB	42.1 dB	6.5 dB	6.5 dB	23.3 dB	21.3 dB	17.5 dB	100 ± 32 Ohm		
350 MHz	38.9 dB/100m	41.1 dB	41.1 dB	2.3 dB	2.3 dB	21.9 dB	19.9 dB	17.0 dB	100 ± 32 Ohm		
400 MHz	42.0 dB/100m	38.3 dB	38.3 dB	-3.7 dB	-3.7 dB	20.8 dB	18.8 dB	16.6 dB	100 ± 32 Ohm		
450 MHz	45.0 dB/100m	37.5 dB	37.5 dB			19.7 dB	17.7 dB	16.2 dB	100 ± 32 Ohm		
500 MHz	47.9 dB/100m	36.8 dB	36.8 dB			18.8 dB	16.8 dB	15.9 dB	100 ± 32 Ohm		
550 MHz	50.6 dB/100m	36.2 dB	36.2 dB			18.0 dB	16.0 dB	15.6 dB	100 ± 32 Ohm		
600 MHz	53.3 dB/100m	35.6 dB	35.6 dB			17.2 dB	15.2 dB	15.4 dB	100 ± 32 Ohm		
650 MHz	55.9 dB/100m	35.1 dB	35.1 dB			16.5 dB	14.5 dB	15.1 dB	100 ± 32 Ohm		

Segregation class according EN50174-2: a

Voltage

UL Voltage Rating

300 V RMS

Temperature Range

Installation Temp Range:	0°C To +50°C
UL Temp Rating:	75°C
Storage Temp Range:	-20°C To +75°C
Operating Temp Range:	-20°C To +75°C

Mechanical Characteristics

Bulk Cable Weight:	25 lbs/1000ft
Max Recommended Pulling Tension:	25 lbs
Min Bend Radius During Installation:	2.5 in
Min Bend Radius/Minor Axis:	1.0 in

Standards

NEC Articles:	800
NEC/(UL) Specification:	CMR
CEC/C(UL) Specification:	CMR
ISO/IEC Compliance:	11801 ed 2.2 (2011) Class E
CPR Euroclass:	Eca
Data Category:	Category 6
ANSI Compliance:	S-116-732-2013 Category 6, ANSI/NEMA WC-66 Category 6
Telecommunications Standards:	ANSI/TIA-568-C.2 Category 6
IEEE Specification:	IEEE 802.3bt Type 1, Type 2, Type 3, Type 4
Third Party Performance Verification:	Category 6

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
--------------------------------	-----

EU Directive 2002/95/EC (RoHS):	Yes
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	Yes
EU CE Mark:	Yes
EU REACH SVHC Compliance (yyyy-mm-dd):	2017-07-10
EU RoHS Compliance Date (yyyy-mm-dd):	2009-04-03
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Aerial:	No
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Non-Halogenated:	No
Suitability - Oil Resistance:	No
Suitability - Outdoor:	No
Suitability - Sunlight Resistance:	No

Flammability, LSOH, Toxicity Testing

C(UL) Flammability:	FT4
UL Flammability:	UL 1666 Riser
ISO/IEC Flammability:	IEC 60332-1-2
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	3613

Part Number

Variants

Item #	Color	UPC	Length	Footnote
3612 0101000	Black	612825145707	1,000 ft	C
3612 010A1000	Black	612825145684	1,000 ft	C
3612 010U1000	Black	612825145691	1,000 ft	
3612 0061000	Blue	612825145585	1,000 ft	C
3612 0062500	Blue	612825145592	2,500 ft	
3612 006A1000	Blue	612825145561	1,000 ft	C
3612 006U1000	Blue	612825145578	1,000 ft	
3612 0081000	Gray	612825145639	1,000 ft	C
3612 008A1000	Gray	612825335061	1,000 ft	C
3612 008U1000	Gray	612825145622	1,000 ft	
3612 0051000	Green	612825145554	1,000 ft	C
3612 005A1000	Green	612825145530	1,000 ft	C
3612 005U1000	Green	612825145547	1,000 ft	
3612 003A1000	Orange	612825145479	1,000 ft	C
3612 003U1000	Orange	612825145486	1,000 ft	
3612 007A1000	Purple	612825145608	1,000 ft	C
3612 007U1000	Purple	612825145615	1,000 ft	
3612 0091000	White	612825145660	1,000 ft	C
3612 0092500	White	612825145677	2,500 ft	
3612 009A1000	White	612825145646	1,000 ft	C

3612 009U1000	White	612825145653	1,000 ft	
3612 0041000	Yellow	612825145516	1,000 ft	C
3612 0042500	Yellow	612825145523	2,500 ft	
3612 004A1000	Yellow	612825145493	1,000 ft	C
3612 004U1000	Yellow	612825145509	1,000 ft	

Footnote:	C - CRATE REEL PUT-UP.
Patent:	https://www.belden.com/resources/patents

Product Notes

Notes:	Values above 400 MHz are for Engineering Information Only. Print Includes Descending Footage/Meter Markings from Max. Put-Up Length to 0.
--------	---

© 2019 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.