



**Part Number: 3633**

**CAT6++ Horizontal Bonded-Pair, 4pr, UTP, LS-PVC Jkt, CMP**

**Product Description**

CAT6++ (400MHz), 4-Bonded-pairs, U/UTP-unshielded, Plenum-CMP, Premise Horizontal cable, 23 AWG solid bare copper conductors, FEP insulation, patented X-spline, ripcord, Flamarrest® PVC jacket.

**Technical Specifications**

**Product Overview**

Environmental Space:	Plenum
Suitable Applications:	Premise Horizontal Cable, Gigabit Ethernet, POE, POE+, 100BaseTX, 100BaseVG ANYLAN, 155ATM, 622ATM, NTSC/PAL Component or Composite Video, AES/EBU Digital Audio, AES51, RS-422, Noisy Environments

**Physical Characteristics (Overall)**

**Conductor**

AWG	Stranding	Material	No. of Pairs
23	Solid	BC - Bare Copper	4

Conductor Count:	8
Total Number of Pairs:	4

**Insulation**

Material	
FEP - Fluorinated Ethylene Propylene	
Bonded-Pair:	Yes

**Color Chart**

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

**Outer Jacket Material**

Material	Material Trade Name	Nominal Diameter	Nominal Wall Thickness	Ripcord	Separator Material
LS PVC - Low Smoke Polyvinyl Chloride	Flamarrest®	0.230 in	0.018 in	Yes	Patented X-Spline Center Member

**Electrical Characteristics**

**Conductor DCR**

Max. Conductor DCR	Max. DCR Unbalance
77 Ohm/km	3 %

**Capacitance**

Max. Capacitance Unbalance	Nom. Mutual Capacitance
90 pF/100m	15.5 pF/ft

**Delay**

Frequency [MHz]	Max. Delay	Max. Delay Skew	Nominal Velocity of Propagation (VP) [%]	Typical Delay Skew
-----------------	------------	-----------------	--	--------------------

100 MHz	537.6 ns/100m	35 ns/100m	72 %	30 ns/100m
---------	---------------	------------	------	------------

## High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted)	Max./Min. Fitted Impedance	Min. TCL [dB]	Min. ELTCTL [dB]
0.772 MHz	1.8 dB/100m	81.0 dB	81.0 dB	79.2 dB	79.2 dB	75.0 dB	73.0 dB				42.0 dB	39.2 dB
1 MHz	2.0 dB/100m	79.3 dB	79.3 dB	77.3 dB	77.3 dB	72.8 dB	70.8 dB	20.0 dB	100 ± 12 Ohm	100 ± 12 Ohm	42.0 dB	37.0 dB
4 MHz	3.7 dB/100m	70.3 dB	70.3 dB	66.6 dB	66.6 dB	60.8 dB	58.8 dB	23.0 dB	100 ± 12 Ohm	100 ± 10.4 Ohm	42.0 dB	25.0 dB
8 MHz	5.2 dB/100m	65.8 dB	65.8 dB	60.6 dB	60.6 dB	54.7 dB	52.7 dB	24.5 dB	100 ± 12 Ohm	100 ± 8 Ohm	42.0 dB	18.9 dB
10 MHz	5.8 dB/100m	64.3 dB	64.3 dB	58.5 dB	58.5 dB	52.8 dB	50.8 dB	25.0 dB	100 ± 12 Ohm	100 ± 7.3 Ohm	42.0 dB	17.0 dB
16 MHz	7.4 dB/100m	61.2 dB	61.2 dB	53.9 dB	53.9 dB	48.7 dB	46.7 dB	25.0 dB	100 ± 12 Ohm	100 ± 5.7 Ohm	40.0 dB	12.9 dB
20 MHz	8.3 dB/100m	59.8 dB	59.8 dB	51.5 dB	51.5 dB	46.8 dB	44.8 dB	25.0 dB	100 ± 12 Ohm	100 ± 5 Ohm	39.0 dB	11.0 dB
25 MHz	9.3 dB/100m	58.3 dB	58.3 dB	49.1 dB	49.1 dB	44.8 dB	42.8 dB	25.0 dB	100 ± 15 Ohm	100 ± 5 Ohm	38.0 dB	9.0 dB
31.25 MHz	10.4 dB/100m	56.9 dB	56.9 dB	46.5 dB	46.5 dB	42.9 dB	40.9 dB	25.0 dB	100 ± 15 Ohm	100 ± 5 Ohm	37.1 dB	
62.5 MHz	15.0 dB/100m	52.4 dB	52.4 dB	37.4 dB	37.4 dB	36.9 dB	34.9 dB	25.0 dB	100 ± 15 Ohm	100 ± 5 Ohm	34.0 dB	
100 MHz	19.3 dB/100m	49.3 dB	49.3 dB	30.0 dB	30.0 dB	32.8 dB	30.8 dB	25.0 dB	100 ± 15 Ohm	100 ± 5 Ohm	32.0 dB	
155 MHz	24.6 dB/100m	46.4 dB	46.4 dB	21.8 dB	21.8 dB	28.9 dB	26.9 dB	22.8 dB	100 ± 15 Ohm	100 ± 5 Ohm	30.1 dB	
200 MHz	28.3 dB/100m	44.8 dB	44.8 dB	16.5 dB	16.5 dB	26.8 dB	24.8 dB	21.6 dB	100 ± 15 Ohm	100 ± 5 Ohm	29.0 dB	
250 MHz	32.1 dB/100m	43.3 dB	43.3 dB	11.2 dB	11.2 dB	24.8 dB	22.8 dB	20.5 dB	100 ± 20 Ohm	100 ± 5 Ohm	28.0 dB	
300 MHz	35.6 dB/100m	42.1 dB	42.1 dB	6.5 dB	6.5 dB	23.3 dB	21.3 dB	20.1 dB	100 ± 20 Ohm	100 ± 5 Ohm		
350 MHz	38.9 dB/100m	41.1 dB	41.1 dB	2.3 dB	2.3 dB	21.9 dB	19.9 dB	19.8 dB	100 ± 22 Ohm	100 ± 5 Ohm		
400 MHz	42.0 dB/100m	38.3 dB	38.3 dB	-3.7 dB	-3.7 dB	20.8 dB	18.8 dB	19.5 dB	100 ± 22 Ohm	100 ± 5 Ohm		
450 MHz	45.0 dB/100m	37.5 dB	37.5 dB			19.7 dB	17.7 dB	18.9 dB	100 ± 22 Ohm	100 ± 5 Ohm		
500 MHz	47.9 dB/100m	36.8 dB	36.8 dB			18.8 dB	16.8 dB	18.4 dB	100 ± 22 Ohm	100 ± 5 Ohm		
550 MHz	50.6 dB/100m	36.2 dB	36.2 dB			18.0 dB	16.0 dB	18.0 dB	100 ± 22 Ohm	100 ± 5 Ohm		
600 MHz	53.3 dB/100m	35.6 dB	35.6 dB			17.2 dB	15.2 dB	17.5 dB	100 ± 22 Ohm	100 ± 5 Ohm		
650 MHz	55.9 dB/100m	35.1 dB	35.1 dB			16.5 dB	14.5 dB	17.2 dB	100 ± 22 Ohm	100 ± 5 Ohm		

Segregation class according EN50174-2: a

## Voltage

<b>UL Voltage Rating</b>
300 V RMS

## Temperature Range

Installation Temp Range:	0°C To +50°C
UL Temp Rating:	105°C
Storage Temp Range:	-20°C To +75°C
Operating Temp Range:	-20°C To +75°C

## Mechanical Characteristics

Bulk Cable Weight:	31 lbs/1000ft
Max Recommended Pulling Tension:	40 lbs
Min Bend Radius During Installation:	2.5 in
Min Bend Radius/Minor Axis:	0.5 in

## Standards

NEC/(UL) Specification:	CMP
CEC/C(UL) Specification:	CMP
ISO/IEC Compliance:	11801 ed 2.2 (2011) Class E
CPR Euroclass:	Eca
Data Category:	Category 6
ANSI Compliance:	S-116-732-2013 Category 6, ANSI/NEMA WC-66 Category 6
Telecommunications Standards:	ANSI/TIA-568-C.2 Category 6
IEEE Specification:	IEEE 802.3bt Type 1, Type 2, Type 3, Type 4
Other Standards:	C(UL)US CMP 105C OR (UL) CMP-LP (0.6A) OR CL3P-LP (0.6A)
Third Party Performance Verification:	Category 6

## Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
--------------------------------	-----

EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	Yes
EU CE Mark:	Yes
EU REACH SVHC Compliance (yyyy-mm-dd):	2017-07-10
EU RoHS Compliance Date (yyyy-mm-dd):	2009-04-03
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

## Suitability

Suitability - Aerial:	No
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Non-Halogenated:	No
Suitability - Oil Resistance:	No
Suitability - Outdoor:	No
Suitability - Sunlight Resistance:	No

## Flammability, LS0H, Toxicity Testing

C(UL) Flammability:	FT6
UL Flammability:	NFPA 262 Plenum (UL 910)
CSA Flammability:	FT6
ISO/IEC Flammability:	IEC 60332-1-2
UL voltage rating:	300 V RMS

## Plenum/Non-Plenum

Plenum (Y/N):	Yes
---------------	-----

## Part Number

Non-Plenum Number:	3632
--------------------	------

## Variants

Item #	Color	UPC	Length	Footnote
3633 0101000	Black	612825146421	1,000 ft	C
3633 010A1000	Black	612825146414	1,000 ft	C
3633 D151000	Blue	612825146261	1,000 ft	C
3633 D15A1000	Blue	612825146247	1,000 ft	C
3633 D15U1000	Blue	612825146254	1,000 ft	
3633 0081000	Gray	612825146377	1,000 ft	C
3633 008A1000	Gray	612825146353	1,000 ft	C
3633 008U1000	Gray	612825146360	1,000 ft	
3633 0051000	Green	612825146346	1,000 ft	C
3633 005A1000	Green	612825146339	1,000 ft	C
3633 0031000	Orange	612825146308	1,000 ft	C
3633 003A1000	Orange	612825146292	1,000 ft	C
3633 0021000	Red	612825146285	1,000 ft	C
3633 002A1000	Red	612825146278	1,000 ft	C
3633 0091000	White	612825146407	1,000 ft	C
3633 009A1000	White	612825146384	1,000 ft	C
3633 009U1000	White	612825146391	1,000 ft	
3633 0041000	Yellow	612825146322	1,000 ft	C
3633 004A1000	Yellow	612825146315	1,000 ft	C

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

Patent:	<a href="https://www.belden.com/resources/patents">https://www.belden.com/resources/patents</a>
---------	---

## Product Notes

Notes:	Values above 400 MHz are for Engineering Information Only. Print Includes Descending Footage/Meter Markings from Max. Put-Up Length to 0.
--------	---

## History

Update and Revision:	Revision Number: 0.361 Revision Date: 08-22-2019
----------------------	--

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.