



Product: [4-2/4-WEM](#)

XTran Interface Module with 4x 4/2 Wire Interfaces (ITU-T G.712 compatible)

Product Description

The 4-2/4WEM interface module (=IFM) can be used to interconnect leased line modems, PABXs... via the XTran Network. This module provides 4 RJ45 ports to transport E&M signaling and analogue voice signals between 300 - 3400Hz. This IFM is compliant with G.712 and supports the G.711 a-Law and μ -Law codec.

Technical Specifications

Product Overview

Part Number:	S30924-Q205-X201
Port Type and Quantity:	4x RJ-45 connectors (balanced voice ports, 600 Ω . Sample rate 8Khz)
Port Mode:	LAN

Power requirements

Operating Voltage:	+12V
Power consumption:	Measured at 25°C/77°F, with data transport: 7.2W

Features and Protocols

Test & Debugging Features:	Test & Loopback, Loss Measurement (LM) (in aggregation/access nodes), Delay Measurement (DM) (in aggregation/access node), Tunnel Ping, Tunnel Traceroute, Port Mirroring (can only be a source, can be mirrored to Ethernet IFMs)
Configurable Services:	Circuit Emulation: SAToP (=Structured Agnostic TDM over Packet), CESoPSN (=Circuit Emulation Service over Packet Switched Network), Point-to-Point/Multipoint: -48VDC E&M Signaling (4 Types: II, III, IV, V), Voice Amplification, Hitless Switching, Single Path

Ambient conditions

MTBF (Telcordia SR-332 Issue 4) @ 25°C:	150 Years
Operating Temperature Range:	With XT-1104-A, XT-2206-A, XT-2209-A, XT-2210-A (aggregation nodes): -30° to +65°C (-22° to 149°F); With XT-2215-A (core nodes): -20° to +55°C (-4° to 131°F)
Storage Temperature Range:	-30° to +75°C (-22° to 167°F)
Relative humidity (non-condensing):	0-95 %

Mechanical construction

Overall Width:	20.32 mm
Overall Height:	126 mm
Depth:	195 mm
Weight:	0.24 kg

Approvals

Basis Standard:	G.712 compliant, G.711 a/ μ -law, CE, EN 55032:2015 + A11:2020, EN IEC 61000-3-2:2019, EN 61000-3-3:2013 + A2 :2021, EN 55035:2017 + A11:2020, EN IEC 61000-6-1:2019, EN IEC 61000-6-2:2019, EN IEC 61000-6-3:2021, EN IEC 61000-6-4:2019
Safety of industrial control equipment:	EN 62368-1:2014
Power Utility:	EN 61000-6-5:2015, EN 61850-3:2014 (§6.7), IEEE 1613-2009 (§4), IEEE1613-2013 (clause 5,7,8,9,10)
Transportation:	EN 50121-4:2016 + A1:2019

Reliability

Guarantee:	Standard 1 year (extension possible)
------------	--------------------------------------

Scope of delivery and accessories

Accessories to Order Separately:	Interface Adapter Kit for Core Nodes: C30965-A9550-D16
----------------------------------	--

Further Instructions

Product Documentation:	Available via Belden Solutions Portal site
Certificates:	Available via Belden Solutions Portal site
Software Download:	Available via Belden Solutions Portal site

History

Update and Revision:	Revision Number: 0.23 Revision Date: 11-14-2025
----------------------	---

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.