



Product: [443945](#)

Surveillance CCTV, RG-59 #20 BC, 90% BC Braid, LSZH Jkt, Eca

Product Description

Surveillance & CCTV Cable, RG59, Rated-CMG, 20 AWG solid bare copper, foam polyolefin core, 90% bare copper braid, LSZH jacket, Eca

Technical Specifications

Product Overview

Suitable Applications:	Coaxial cable used in analogue video and CCTV communication networks designed according European Standard EN 50117-1; Operating at frequencies between 5 and 1000 MHz
------------------------	---

Construction Details

RG Type:	59
----------	----

Conductor

No. of Elements	Size	Stranding	Nom. Diameter	Material
1	20 AWG	Solid	0.81 mm	BC - Bare Copper

Insulation

Material	Nom. Insulation Diameter
PE - Polyethylene (Foam)	3.68 mm (0.145 in)

Outer Shield

Outer Shield Type	Material	Coverage
Braid	Bare Copper (BC)	95%

Outer Jacket

Material	Nom. Diameter
LSZH - Low Smoke Zero Halogen (Flame Retardant)	5.9 mm

Electrical Characteristics

Attenuation

Frequency	Nom. Attenuation
1 MHz	0.98 dB/100m
5 MHz	2.13 dB/100m
10 MHz	2.95 dB/100m
50 MHz	6.23 dB/100m
100 MHz	8.53 dB/100m
200 MHz	11.8 dB/100m
400 MHz	16.4 dB/100m
700 MHz	23 dB/100m
900 MHz	26.2 dB/100m
1000 MHz	27.9 dB/100m

Electricals

Nom. Conductor DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Characteristic Impedance	Nom. Velocity of Prop.
33.5 Ohm/km	12.48 Ohm/km (3.804 Ohm/1000ft)	55.6 pF/m (16.9 pF/ft)	75 Ohm	83%

Mechanical Characteristics

Temperature

Operating	Storage
-30°C To +70°C	-30°C To +70°C

Bend Radius

Stationary Min.	Installation Min.
29.5 mm (1.16 in)	59 mm

Bulk Cable Weight: 43 kg/km

Standards and Compliance

Environmental Suitability:	Indoor - Euroclass Eca
Flammability / Reaction to Fire:	IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
UK Regulation Compliance:	UKCA Mark

History

Update and Revision: Revision Number: 0.250 Revision Date: 02-03-2025

Part Numbers

Variants

Item #	Color	Putup Type	Length	EAN
443945.01305	Black	Reel	305 m	8719605006998
443945.01500	Black	Reel	500 m	8719605170408
443945.011524	Black	Reel	1,524 m	8719605006981
443945.00100	Gray	Reel	100 m	8719605006950
443945.00999	Gray	Reel	499 m	8719605006974
443945.00500	Gray	Reel	500 m	8719605006967

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.