



Product: [4794RBUHD1 B50](#)

12 GHz Series 7 BNC Connector

Product Description

Series 7, 12 GHz, UHD, BNC, 1 piece connector

Technical Specifications

Physical Characteristics (Overall)

Packaging:	25 Pack
------------	---------

Connectors

Materials

Description	Material
Nut	Polished Nickel
Body	Polished Nickel
Contact	Brass, Gold Plated
Insulator	PTFE

Electrical Characteristics

Impedance

Nominal Characteristic Impedance
75 Ohm

Return Loss (RL)

Frequency [MHz]	Minimum Return (RL)
5-1485	15 dB
1485-3000	10 dB
3000-6000	7 dB
6000-12000	4 dB

Electrical Characteristics Notes:	SMPTE 2082-1 Return Loss or better
-----------------------------------	------------------------------------

Mechanical Characteristics

Footprint/Type:	Coax
Connector Interface Type:	BNC
Gender:	Male - plug
Connector Series Name:	UHD
Color Band:	White
Locking:	No
Tool Compatibility:	CPLCRBC1794 (Compression), PS-11 (Strip)
Termination Type:	Compression
Cable Center Conductor Diameter Limits:	0.0460 - 0.0519 in
Cable Dielectric Diameter Limits:	0.2283 - 0.2362 in
Cable Outer Jacket Diameter Limits:	0.3110 - 0.3267 in

Standards

RG Type:	Series 7
----------	----------

Applicable Environmental and Other Programs

Environmental Space:	Indoor
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
CA Prop 65:	Yes

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	No

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	UPC
4794RBUHD1 B50	White	845671005561

History

Update and Revision:	Revision Number: 0.26 Revision Date: 01-31-2020
----------------------	---

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.