



**Product:** [4302UE](#)

Security & Sound, 4 Conductor 18 AWG BC, LSZH, Eca

## Product Description

Security & Commercial Audio Cable, 4-18 AWG stranded bare copper conductors with polypropylene insulation, LSZH jacket with ripcord, CPR Eca

## Technical Specifications

### Product Overview

Suitable Applications:	Security System, Intercom/PA, Audio/Speaker, Power-Limited Controls
------------------------	---

### Physical Characteristics (Overall)

#### Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Conductors
18	7x26	BC - Bare Copper	1.22 mm	4

Conductor Count:	4
------------------	---

#### Insulation

Type	Material	Nominal Diameter	Diameter +/- Tolerance	Nominal Wall Thickness
Insulation	PP - Polypropylene	1.5 mm	0.05 mm	0.2 mm

#### Color Chart

Number	Color
Wire 1	Black
Wire 2	Red
Wire 3	White
Wire 4	Green

#### Outer Jacket

Material	Nominal Diameter	Nominal Wall Thickness	Ripcord
LSZH - Low Smoke Zero Halogen (Flame Retardant)	4.7 mm	0.4 mm	Yes

Table Notes:	Ripcord provided under sheath
--------------	-------------------------------

### Construction and Dimensions

#### Cabling

Description
4 wires twisted

### Electrical Characteristics

#### Conductor DCR

Nominal Conductor DCR
21.3 Ohm/km

#### Capacitance

Nom. Capacitance Conductor to Conductor
70 pF/m

## Current

### Max. Recommended Current [A]

4 A

## Voltage

### Voltage Rating [V]

300 V

## Temperature Range

Installation Temperature Range:	-20°C To +70°C
Storage Temperature Range:	-30°C To +70°C
Operating Temperature Range:	-20°C To +70°C

## Mechanical Characteristics

Max. Pull Tension:	180 N
Min. Bend Radius During Installation:	47 mm
Min Setting Radius:	23.5 mm

## Standards

CPR Euroclass:	Eca
----------------	-----

## Applicable Environmental and Other Programs

Environmental Space:	Indoor - Euroclass Eca
----------------------	------------------------

## Flammability, LSOH, Toxicity Testing

IEC Flammability:	IEC 60332-1-2
IEC 60754-1 - Halogen Amount:	Zero
IEC 60754-2 - Halogen Acid Gas Amount - Max. Conductivity:	2.5 µS/mm
IEC 60754-2 - Halogen Acid Gas Amount - Min. pH:	4.3
IEC 61034-2 - Smoke Density Min. Transmittance:	60%

## Related Part Numbers

## Variants

Item #	Color	Put-Up Type	Length	EAN
4302UE.00100	Gray	Reel	100 m	8719605006646
4302UE.00500	Gray, RAL 7032	Reel	500 m	8719605006653

## History

Update and Revision:	Revision Number: 0.294 Revision Date: 03-04-2025
----------------------	--

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.