


**Product:** [4542UE](#) 



Security & Sound, 3 Pair 22 AWG BC, LSZH

## Product Description

Security & Commercial Audio Cable, 3-22 AWG stranded bare copper pairs with polypropylene insulation, LSZH jacket with ripcord

## Technical Specifications

### Product Overview

Suitable Applications:	Security Systems, Intercom/PA Systems, Sound/Audio Systems Power-Limited Controls
------------------------	---

### Physical Characteristics (Overall)

#### Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Pairs
22	7x30	BC - Bare Copper	0.75 mm	3

Conductor Count:	6
Total Number of Pairs:	3

#### Insulation

Material	Nominal Diameter	Diameter +/- Tolerance	Nominal Wall Thickness
PE - Polyethylene	1.07 mm	0.05 mm	0.2 mm

#### Color Chart

Number	Color
Pair 1	Black & Red
Pair 2	Black & White
Pair 3	Black & Green

#### Outer Shield Material

Material
No Shield

#### Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
LSZH - Low Smoke Zero Halogen (Flame Retardant)	5 mm	0.38 mm

### Construction and Dimensions

#### Cabling

Description
3 pairs twisted to cable core

### Electrical Characteristics

#### Conductor DCR

Nominal Conductor DCR
54 Ohm/km

#### Capacitance

Nom. Capacitance Conductor to Conductor
100 pF/m

#### Current

Element	Max. Recommended Current [A]
Conductor	2 A

#### Voltage

Voltage Rating [V]
300 V

#### Temperature Range

Storage Temp Range:	-30°C to +70°C
Operating Temp Range (Fixed Install):	-20°C To +70°C

#### Mechanical Characteristics

Max. Pull Tension:	130 N
Min Bend Radius During Installation:	25 mm
Min Setting Radius:	50 mm

#### Applicable Environmental and Other Programs

Environmental Space:	Indoor
EU RoHS Compliance Date (yyyy-mm-dd):	2013-10-02

#### Flammability, LS0H, Toxicity Testing

IEC 60754-1 (EN50267-1)- Halogen Amount:	Zero
--	------

#### Part Number

#### Variants

Item #	Color	Putup Type	Length	EAN
4542UE.00500	Gray	Reel	500 m	8719605007346

#### History

Update and Revision:	Revision Number: 0.181 Revision Date: 10-06-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.