



Product: [46383NH](#)

Speaker Cable LSZH 4x4.0mm², CPR Eca.

Product Description

Speaker Cable, 4 Conductor 4.0mm² (56 x 0.30mm) Oxygen-Free Bare Copper (High Conductivity), PE Insulation, LSZH Jacket, Flexible, CPR Euroclass Eca.

Technical Specifications

Product Overview

Suitable Applications:	Speaker cable for use in indoor or outdoor applications
------------------------	---

Physical Characteristics (Overall)

Conductor

Stranding	Cross Section	Construction n x D
Stranded	4.00 mm ²	56x0.30 mm

Conductor Count:	4
------------------	---

Insulation

Type	Material	Nominal Diameter	Diameter +/- Tolerance
Insulation	LSZH - Low Smoke Zero Halogen (Flame Retardant)	3.50 mm	0.07 mm

Color Chart

Number	Color
Wire 1	Black
Wire 2	Red
Wire 3	White
Wire 4	Green

Outer Jacket

Material	Nominal Diameter	Diameter +/- Tolerance
LSZH - Low Smoke Zero Halogen (Flame Retardant)	11.00 mm	0.30 mm

Construction and Dimensions

Cabling

Description	Filler
1 center filler + 4 wires twisted	PP (1.50mm)

Electrical Characteristics

Conductor DCR

Max. Conductor DCR
4.5 Ohm/km

Temperature Range

Storage Temperature Range:	-40°C To +70°C
Operating Temperature Range:	-40°C To +70°C

Standards

CPR Euroclass:	Eca
----------------	-----

Applicable Environmental and Other Programs

Environmental Space:	Indoor/Outdoor
----------------------	----------------

Flammability, LSOH, Toxicity Testing

IEC Flammability:	IEC 60332-1-2
IEC 60754-1 - Halogen Amount:	Zero
IEC 60754-2 - Halogen Acid Gas Amount - Max. Conductivity:	2.5 µS/mm
IEC 60754-2 - Halogen Acid Gas Amount - Min. pH:	4.3

Related Part Numbers

Variants

Item #	Color	Put-Up Type	Length	EAN
46383NH.00305	Black	Reel	305 m	8719605144256
46383NH.00500	Black	Reel	500 m	8719605144263

History

Update and Revision:	Revision Number: 0.90 Revision Date: 12-20-2022
----------------------	---

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.