



REPRESENTATIVE IMAGE

**Product:** [4T01ULW](#)

Security & Sound, 3 Conductor 10 AWG BC, LSZH, Cca

## Product Description

Security & Commercial Audio Cable, 3-10 AWG stranded bare copper conductors with Low Smoke Zero Halogen insulation, LSZH jacket with ripcord, CPR Cca

## Technical Specifications

### Product Overview

Suitable Applications:	Intercom/PA Systems, Sound/Audio Systems, Control Systems
------------------------	---

### Physical Characteristics (Overall)

#### Conductor

AWG	Stranding	Material	No. of Conductors
10	65x28	BC - Bare Copper	3

Conductor Count:	3
------------------	---

#### Insulation

Material	Nominal Diameter	Diameter +/- Tolerance	Nominal Wall Thickness
LSZH - Low Smoke Zero Halogen (Flame Retardant)	4.0 mm	0.05 mm	0.2 mm

#### Outer Jacket

Material	Nominal Diameter	Nominal Wall Thickness	Ripcord
LSZH - Low Smoke Zero Halogen (Flame Retardant)	11.6 mm	1.3 mm	Yes

Table Notes:	Ripcord provided under sheath
--------------	-------------------------------

### Electrical Characteristics

#### Conductor DCR

<b>Nominal Conductor DCR</b>
3.2 Ohm/km

#### Capacitance

<b>Nom. Capacitance Conductor to Conductor</b>
100 pF/m

#### Voltage

<b>Voltage Rating [V]</b>
300 V

### Temperature Range

Installation Temperature Range:	-20°C To +70°C
Storage Temperature Range:	-30°C To +70°C

### Mechanical Characteristics

Max. Pull Tension:	750 N
Min. Bend Radius During Installation:	116 mm

Min Setting Radius:	58 mm
---------------------	-------

## Standards

CPR Euroclass:	Cca-s1,d1,a1
----------------	--------------

## Applicable Environmental and Other Programs

Environmental Space:	Indoor - Euroclass Cca
----------------------	------------------------

## Flammability, LSOH, Toxicity Testing

IEC Flammability:	IEC 60332-1-2
IEC 60754-2 - Halogen Acid Gas Amount - Max. Conductivity:	2.5 µS/mm
IEC 60754-2 - Halogen Acid Gas Amount - Min. pH:	4.3
IEC 61034-2 - Smoke Density Min. Transmittance:	60%

## Related Part Numbers

### Variants

Item #
4T01ULW.00500

## History

Update and Revision:	Revision Number: 0.15 Revision Date: 06-13-2024
----------------------	---

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.