



**Product:** [4694P](#)

4K UHD Coax for 12G-SDI, 75 Ohm, RG-6, 18 AWG Solid SC, Foil + 95% TC Braid, PVC Jkt, CMP

### Product Description

75 Ohm SDI Coax, RG-6, 18 AWG Solid Silvered Copper Conductor, FEP Insulation, Foil + 95% Tinned Copper Braid Shield, PVC Jacket, CMP

### Technical Specifications

#### Product Overview

Suitable Applications:	Ultra-High Definition Digital Video, 4K Single-link 12 Gb/s UHD TV, 4K D-Cinema, 8K Quad-link UHD TV, HD-SDI 1080p
------------------------	--

#### Construction Details

RG Type:	6
----------	---

#### Conductor

Size	Stranding	Nom. Diameter	Material
18 AWG	Solid	0.040 in	SC - Silvered Copper

#### Insulation

Material	Nom. Insulation Diameter
FEP - Fluorinated Ethylene Propylene (Foam)	0.168 in (4.27 mm)

#### Outer Shield

Layer	Outer Shield Type	Material	Material Trade Name	Coverage
1	Tape	Tri-Laminate (Alum+Poly+Alum)	Duobond® II	100%
2	Braid	Tinned Copper (TC)		95%

#### Outer Jacket

Material	Nom. Diameter
PVC - Polyvinyl Chloride	0.229 in (5.82 mm)

Overall Cable Diameter (Nominal):	0.229 in (5.82 mm)
-----------------------------------	--------------------

#### Electrical Characteristics

#### Return Loss (RL)

Frequency	Min. Return Loss
5 - 1600 MHz	23 dB
1600 - 4500 MHz	21 dB
4500 - 12000 MHz	15 dB

#### Electricals

Nom. Conductor DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Characteristic Impedance	Nom. Velocity of Prop.
6.4 Ohm/1000ft (21 Ohm/km)	2.9 Ohm/1000ft (9.5 Ohm/km)	16.1 pF/ft (52.8 pF/m)	75 Ohm	83%

#### Voltage

UL Voltage Rating
300 V (CMP)

#### Mechanical Characteristics

## Temperature

UL Temperature	Operating
60°C	0°C to +75°C

## Bend Radius

Installation Min.
2.3 in

Max. Pull Tension:	69 lbs (31 kg)
Bulk Cable Weight:	41 lbs/1000ft

## Standards and Compliance

Environmental Suitability:	Indoor - Plenum, Indoor, Aerial - Black only, When supported by messenger wire
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	NFPA 262
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	CMP
CEC / C(UL) Compliance:	CMP
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Non-Plenum Number:	4694R

## History

Update and Revision:	Revision Number: 0.164 Revision Date: 12-19-2022
----------------------	--

## Part Numbers

### Variants

Item #	Color	Putup Type	Length	UPC
4694P 0101000	Black	Reel	1,000 ft	612825406808
4694P 0105000	Black	Reel	5,000 ft	612825406815
4694P 0061000	Blue, Light	Reel	1,000 ft	612825406785
4694P N3U1000	Green, Mil	Reel	1,000 ft	612825406754
4694P 0031000	Orange	Reel	1,000 ft	612825406778
4694P 0021000	Red	Reel	1,000 ft	612825406761
4694P 0071000	Violet	Reel	1,000 ft	612825406792

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.