


**Part Number: 5000FE**

Security & Sound, 2 Conductor 12 AWG, BC, O/A Foil, CMR



### Product Description

Security & Commercial Audio Cable, Riser-CL3R-FPLR, 2-12 AWG stranded bare copper conductors with Polyolefin insulation, Beldfoil® shield and PVC jacket with ripcord

### Technical Specifications

#### Product Overview

Environmental Space:	Indoor - Riser
Suitable Applications:	Intercom/PA Systems, Sound/Audio Systems, Fire Alarm Systems (For color Red only)

#### Physical Characteristics (Overall)

##### Conductor

AWG	Stranding	Material	No. of Conductors
12	19x25	BC - Bare Copper	2

Conductor Count:	2
Conductor Size:	12 AWG

##### Insulation

Material	Nominal Wall Thickness
PP - Polypropylene	0.011 in

##### Color Chart

Number	Color
1	Black
2	White

##### Outer Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Aluminum/Polyester	Beldfoil®	100 %	TC - Tinned Copper	20	Solid

##### Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness	Ripcord
PVC - Polyvinyl Chloride	0.264 in	0.017 in	Yes

#### Construction and Dimensions

##### Cabling

Lay Direction	Twists
Left Hand	3.4 twist/ft

#### Electrical Characteristics

##### Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR
1.6 Ohm/1000ft	7.1 Ohm/1000ft

## Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
64 pF/ft	115.25 pF/ft

## Inductance

Nominal Inductance
0.14 µH/ft

## Current

Element	Max. Recommended Current [A]
10C Temperature Rise	12 Amps per conductor @ 25°C ambient

## Voltage

UL Voltage Rating
300 V RMS

## Temperature Range

UL Temp Rating:	75°C
Operating Temp Range:	-20°C To +75°C

## Mechanical Characteristics

Bulk Cable Weight:	62.5 lbs/1000ft
Max Recommended Pulling Tension:	182.4 lbs
Min Bend Radius/Minor Axis:	2.625 in

## Standards

NEC Articles:	725, 760
NEC/(UL) Specification:	CL3R, FPLR
CPR Euroclass:	Eca

## Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

## Suitability

Suitability - Indoor:	Yes
-----------------------	-----

## Flammability, LSOH, Toxicity Testing

UL Flammability:	UL1666 Vertical Shaft
CSA Flammability:	FT4
UL voltage rating:	300 V RMS

## Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	6000FE

## Part Number

### Variants

Item #	Color	Footnote
5000FE 0081000	Gray	C
5000FE 008500	Gray	C
5000FE 0021000	Red	C

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.