



Product: [4794RX5](#)

12 GHz 5 Coax, 4K UHD Precision Video Cable, RG-7 Series, 75 Ohm, 16 AWG Solid, CMR

### Product Description

12 GHz, 4K UHD Precision Video Cable, RG-7 Series, 75 Ohm 5 Coax 16 AWG solid 0.051" silver-plated copper conductor, gas-injected foamed high-density polyethylene insulation, Duofoil® bonded to the core + tinned copper braid shield (95% coverage) plus Beldfoil® with shorting fold, PVC inner and outer jackets

### Technical Specifications

#### Product Overview

Suitable Applications:	SMPTE 2082-1 12 Gb/s UHDTV, SMPTE 2081-1 6 Gb/s UHDTV, SMPTE 424M 3 Gb/s HD-SDI 1080p
------------------------	---

#### Physical Characteristics (Overall)

##### Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Coax
16	Solid	SC - Silvered Copper	0.051 in	5

##### Insulation

Material	Nominal Diameter
PE - Polyethylene (Foam)	0.225 in

Table Notes:	Gas Injected
--------------	--------------

##### Inner Shield

Type	Layer	Material	Material Trade Name	Coverage [%]
Tape	1	Tri-Laminate (Alum+Poly+Alum)	Duofoil®	100%
Braid	2	Tinned Copper (TC)		95%
Tape	3	Bi-Laminate (Alum+Poly)	Beldfoil®	100%

##### Inner Jacket

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.320 in

##### Outer Jacket

Material	Nominal Diameter
PVC - Polyvinyl Chloride	1.068 in

#### Electrical Characteristics

##### Conductor DCR

Nominal Conductor DCR	Outer Conductor DCR
4.0 Ohm/1000ft	1.9 Ohm/1000ft

##### Capacitance

Nom. Capacitance Conductor to Shield
16.0 pF/ft

##### Impedance

Nominal Characteristic Impedance
75 Ohm

**Return Loss (RL)**

Frequency [MHz]	Minimum Return (RL)
5 MHz - 1600 MHz	23 dB
1600 MHz - 4500 MHz	21 dB
4500 MHz - 12000 MHz	15 dB

**High Frequency (Nominal/Typical)**

Frequency [MHz]	Nom. Insertion Loss
1 MHz	0.26 dB/100ft
3.58 MHz	0.43 dB/100ft
5 MHz	0.50 dB/100ft
6 MHz	0.52 dB/100ft
7 MHz	0.55 dB/100ft
10 MHz	0.63 dB/100ft
12 MHz	0.66 dB/100ft
25 MHz	0.88 dB/100ft
55 MHz	1.21 dB/100ft
67.5 MHz	1.31 dB/100ft
71.5 MHz	1.34 dB/100ft
88.5 MHz	1.47 dB/100ft
100 MHz	1.54 dB/100ft
135 MHz	1.75 dB/100ft
143 MHz	1.79 dB/100ft
180 MHz	1.98 dB/100ft
270 MHz	2.47 dB/100ft
360 MHz	2.86 dB/100ft
540 MHz	3.53 dB/100ft
720 MHz	4.09 dB/100ft
750 MHz	4.18 dB/100ft
1000 MHz	4.85 dB/100ft
1500 MHz	5.99 dB/100ft
2000 MHz	6.96 dB/100ft
2250 MHz	7.42 dB/100ft
3000 MHz	8.66 dB/100ft
4500 MHz	10.99 dB/100ft
6000 MHz	12.98 dB/100ft
12000 MHz	19.94 dB/100ft

**Delay**

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.21 ns/ft	84%

**Voltage**

UL Voltage Rating
300 V RMS

Electrical Characteristics Notes:	Return Loss: Fixed bridge and termination
-----------------------------------	---

**Temperature Range**

Operating Temperature Range:	-20°C To +75°C
------------------------------	----------------

**Mechanical Characteristics**

Bulk Cable Weight:	438 lbs
Max. Pull Tension:	420 lbs
Min Bend Radius (Overall):	10.7 in
Min Bend Radius (Each Coax):	3.2 in

**Standards**

NEC/(UL) Compliance:	CMR
CEC/C(UL) Compliance:	CMG
Series Type:	7

## Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2000/53/EC (ELV); EU Directive 2002/96/EC (WEEE); EU Directive 2003/11/EC (BFR); EU Directive 2011/65/EU (ROHS II)
EU CE Mark:	Yes
EU REACH SVHC Compliance (yyyy-mm-dd):	2019-04-01

## Suitability

Suitability - Aerial:	Yes - Black only, when supported by messenger wire
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes - Black only

## Flammability, LSOH, Toxicity Testing

UL Flammability:	UL1666 Vertical Shaft
------------------	-----------------------

## Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

## Related Part Numbers

### Variants

Item #	Color	Put-Up Type	Length	UPC
4794RX5 B59CUT	Black, Matte	Reel		
4794RX5 B59500	Black, Matte	Reel	500 ft	612825443230

## History

Update and Revision:	Revision Number: 0.114 Revision Date: 04-29-2024
----------------------	--

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.