



**Part Number: 4812**

**CAT6"E" Horizontal, 4pr, UTP, PVC Jkt, CMR**

## Product Description

CAT6 Enhanced (600MHz), 4-Pair, U/UTP-unshielded, Riser-CMR, Premise Horizontal cable, 23 AWG solid bare copper conductors, polyolefin insulation, X-spline, ripcord, PVC jacket

## Technical Specifications

### Product Overview

Environmental Space:	Riser
Suitable Applications:	Premise Horizontal Cable, Gigabit Ethernet, 100BaseTX, 100BaseVG ANYLAN, 155ATM, 622ATM, NTSC/PAL Component or Composite Video, AES/EBU Digital Audio, AES51, RS-422, Noisy Environments

### Physical Characteristics (Overall)

#### Conductor

AWG	Stranding	Material	No. of Pairs
23	Solid	BC - Bare Copper	4

Conductor Count:	8
Total Number of Pairs:	4
Conductor Size:	23 AWG

#### Insulation

<b>Material</b>	
PO - Polyolefin	
Bonded-Pair:	N/A

#### Color Chart

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

#### Outer Jacket Material

Material	Nominal Diameter	Ripcord	Separator Material
PVC - Polyvinyl Chloride	0.255 in	Yes	Patented X-Spline Center Member

### Electrical Characteristics

#### Conductor DCR

Max. Conductor DCR	Max. DCR Unbalance	Max DCR Unbalanced Between Pairs [%]
67 Ohm/km	3 %	5 %

#### Capacitance

Max. Capacitance Unbalance	Nom. Mutual Capacitance
90 pF/100m	15.5 pF/ft

#### Delay

Frequency [MHz]	Max. Delay	Max. Delay Skew	Nominal Velocity of Propagation (VP) [%]
100 MHz	537.6 ns/100m	45 ns/100m	68 %

#### High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted)	Max./Min. Fitted Impedance	Min. TCL [dB]	Min. ELTCTL [dB]
0.772 MHz	1.7 dB/100m	83.0 dB	82.0 dB	81.3 dB	80.3 dB	77.0 dB	75.0 dB			102 ± 15 Ohm	40.0 dB	37.2 dB
1 MHz	1.9 dB/100m	81.3 dB	80.3 dB	79.4 dB	78.4 dB	74.8 dB	72.8 dB	20.0 dB	100 ± 15 Ohm	100 ± 15 Ohm	40.0 dB	35.0 dB
4 MHz	3.5 dB/100m	72.3 dB	71.3 dB	68.8 dB	67.8 dB	62.8 dB	60.8 dB	23.0 dB	100 ± 15 Ohm	100 ± 15 Ohm	40.0 dB	23.0 dB
8 MHz	4.9 dB/100m	67.8 dB	66.8 dB	62.8 dB	61.8 dB	56.7 dB	54.7 dB	24.5 dB	100 ± 15 Ohm	100 ± 15 Ohm	40.0 dB	16.9 dB
10 MHz	5.5 dB/100m	66.3 dB	65.3 dB	60.8 dB	59.8 dB	54.8 dB	52.8 dB	25.0 dB	100 ± 15 Ohm	100 ± 15 Ohm	40.0 dB	15.0 dB
16 MHz	7.0 dB/100m	63.2 dB	62.2 dB	56.3 dB	55.3 dB	50.7 dB	48.7 dB	25.0 dB	100 ± 15 Ohm	100 ± 15 Ohm	38.0 dB	10.9 dB
20 MHz	7.8 dB/100m	61.8 dB	60.8 dB	54.0 dB	53.0 dB	48.8 dB	46.8 dB	25.0 dB	100 ± 15 Ohm	100 ± 15 Ohm	37.0 dB	9.0 dB
25 MHz	8.7 dB/100m	60.3 dB	59.3 dB	51.6 dB	50.6 dB	46.8 dB	44.8 dB	25.0 dB	100 ± 15 Ohm	100 ± 15 Ohm	36.0 dB	7.0 dB
31.25 MHz	9.8 dB/100m	58.9 dB	57.9 dB	49.1 dB	48.1 dB	44.9 dB	42.9 dB	24.3 dB	100 ± 15 Ohm	100 ± 15 Ohm	35.1 dB	
62.5 MHz	14.1 dB/100m	54.4 dB	53.4 dB	40.3 dB	39.3 dB	38.9 dB	36.9 dB	22.2 dB	100 ± 15 Ohm	100 ± 15 Ohm	32.0 dB	
100 MHz	18.0 dB/100m	51.3 dB	50.3 dB	33.3 dB	32.3 dB	34.8 dB	32.8 dB	20.8 dB	100 ± 15 Ohm	100 ± 15 Ohm	30.0 dB	
155 MHz	22.8 dB/100m	48.4 dB	47.4 dB	25.7 dB	24.7 dB	31.0 dB	29.0 dB	19.5 dB	100 ± 22 Ohm	100 ± 15 Ohm	28.1 dB	
200 MHz	26.2 dB/100m	46.8 dB	45.8 dB	20.6 dB	19.6 dB	28.8 dB	26.8 dB	18.7 dB	100 ± 22 Ohm	100 ± 15 Ohm	27.0 dB	
250 MHz	29.6 dB/100m	45.3 dB	44.3 dB	15.8 dB	14.8 dB	26.8 dB	24.8 dB	18.0 dB	100 ± 32 Ohm	100 ± 15 Ohm	26.0 dB	
300 MHz	32.7 dB/100m	44.1 dB	43.1 dB	11.4 dB	10.4 dB	25.3 dB	23.3 dB	17.5 dB	100 ± 32 Ohm	100 ± 15 Ohm		
350 MHz	35.6 dB/100m	43.1 dB	42.1 dB	7.5 dB	6.5 dB	23.9 dB	21.9 dB	17.0 dB	100 ± 32 Ohm	100 ± 15 Ohm		
400 MHz	38.4 dB/100m	42.3 dB	41.3 dB	3.9 dB	2.9 dB	22.8 dB	20.8 dB	16.6 dB	100 ± 32 Ohm	100 ± 15 Ohm		
450 MHz	41.0 dB/100m	41.5 dB	40.5 dB	0.5 dB		21.7 dB	19.7 dB	16.2 dB	100 ± 32 Ohm	100 ± 15 Ohm		
500 MHz	43.6 dB/100m	40.8 dB	39.8 dB			20.8 dB	18.8 dB	15.9 dB	100 ± 32 Ohm	100 ± 15 Ohm		
550 MHz	46.0 dB/100m	40.2 dB	39.2 dB			20.0 dB	18.0 dB	15.6 dB	100 ± 32 Ohm	100 ± 15 Ohm		
600 MHz	48.4 dB/100m	39.6 dB	38.6 dB			19.2 dB	17.2 dB	15.4 dB	100 ± 32 Ohm	100 ± 15 Ohm		
650 MHz	50.6 dB/100m	39.1 dB	36.1 dB			18.5 dB	15.5 dB	15.1 dB				
750 MHz	55.0 dB/100ft	38.2 dB	35.2 dB			17.3 dB	14.3 dB	14.7 dB				
860 MHz	59.6 dB/100ft	37.3 dB	34.3 dB			16.1 dB	13.1 dB	14.3 dB				

Segregation class according EN50174-2: a

#### Voltage

##### UL Voltage Rating

300 V RMS

#### Temperature Range

Installation Temp Range:	0°C To +50°C
UL Temp Rating:	75°C
Storage Temp Range:	-20°C To +75°C
Operating Temp Range:	-20°C To +75°C

#### Mechanical Characteristics

Bulk Cable Weight:	31 lbs/1000ft
Max Recommended Pulling Tension:	25 lbs
Min Bend Radius During Installation:	2.75 in
Min Bend Radius/Minor Axis:	1.0 in

#### Standards

NEC Articles:	800
NEC/(UL) Specification:	CMR
CEC/C(UL) Specification:	CMR
ISO/IEC Compliance:	11801 ed 2.2 (2011) Class E
CPR Euroclass:	Eca
Data Category:	Category 6
ANSI Compliance:	S-116-732-2013 Category 6, ANSI/NEMA WC-66 Category 6
Telecommunications Standards:	ANSI/TIA-568-C.2 Category 6
IEEE Specification:	IEEE 802.3bt Type 1, Type 2, Type 3, Type 4
Other Standards:	C(UL)US CMR 75C OR (UL) CMR-LP (0.5A) OR CL3R-LP (0.5A)
Third Party Performance Verification:	Category 6

## Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	Yes
EU CE Mark:	Yes
EU REACH SVHC Compliance (yyyy-mm-dd):	2017-07-10
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

## Suitability

Suitability - Aerial:	No
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Non-Halogenated:	No
Suitability - Oil Resistance:	No
Suitability - Outdoor:	No
Suitability - Sunlight Resistance:	No

## Flammability, LSOH, Toxicity Testing

C(UL) Flammability:	FT4
UL Flammability:	UL 1666 Riser
ISO/IEC Flammability:	IEC 60332-1-2
UL voltage rating:	300 V RMS

## Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	4813

## Part Number

### Variants

Item #	Color	UPC	Length
4812 0103000	Black	612825153573	3,000 ft
4812 0103000	Black	612825153573	3,000 ft
4812 0061000	Blue	612825153528	1,000 ft
4812 0061000	Blue	612825153528	1,000 ft
4812 0062500	Blue	612825153535	2,500 ft
4812 0062500	Blue	612825153535	2,500 ft
4812 006A1000	Blue	612825153511	1,000 ft
4812 006A1000	Blue	612825153511	1,000 ft
4812 0081000	Gray	612825153542	1,000 ft
4812 0081000	Gray	612825153542	1,000 ft
4812 0051000	Green	612825153504	1,000 ft
4812 0051000	Green	612825153504	1,000 ft
4812 0021000	Red	612825153481	1,000 ft
4812 0021000	Red	612825153481	1,000 ft
4812 0091000	White	612825153566	1,000 ft
4812 0091000	White	612825153566	1,000 ft
4812 009A1000	White	612825153559	1,000 ft

4812 009A1000	White	612825153559	1,000 ft
4812 0041000	Yellow	612825153498	1,000 ft
4812 0041000	Yellow	612825153498	1,000 ft

Patent: <https://www.belden.com/resources/patents>

## Product Notes

Notes: Values above 600 MHz are for Engineering Information Only. Print Includes Descending Footage/Meter Markings from Max. Put-Up Length to 0.

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.