



**Product:** [5100F2](#)

Security & Sound, #14-2c, BC, Overall Shield, CL3, FPL, PLTC, Water-Blocked Direct Burial

**Product Description**  
Security & Sound Cable, Rated-CL3, 2-14 AWG PVC-Nylon insulation, 100% Al. Foil Shield, Waterblocking tape, PVC jacket with ripcord

**Technical Specifications**

**Product Overview**

Suitable Applications:	Security System, Intercom/PA, Audio/Speaker, Power-Limited Controls, Wet Location, Direct Burial
------------------------	--

**Construction Details**

<b>Conductor</b>				
Element	No. of Elements	Size	Stranding	Material
Conductor(s)	2	14 AWG	19x27	BC - Bare Copper

<b>Insulation</b>			
Element	Material	Nom. Thickness	Color Code
Conductor(s)	PVC/Nylon - Polyvinyl Chloride + Nylon	.020 in (0.51 mm)	Black, Red

<b>Outer Shield</b>				
Shield Type	Material	Coverage	Drainwire Type	Notes
Tape	Bi-Laminate (Alum+Poly)	100%	24 AWG (7x32) TC	Waterblocking Tape
Waterblocking:		Waterblock Tape		

<b>Outer Jacket</b>			
Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	.040 in (1.0 mm)	.350 in (8.89 mm)	Yes
Table Notes:		Waterblocking Tape	
Overall Cable Diameter (Nominal):		.350 in (8.89 mm)	

**Electrical Characteristics**

<b>Electricals</b>		
Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)
2.7 Ohm/1000ft (8.9 Ohm/km)	46 pF/ft (150 pF/m)	83 pF/ft (270 pF/m)

<b>Voltage</b>
UL Voltage Rating
300 V

**Mechanical Characteristics**

<b>Temperature</b>	
UL Temperature	Operating
90°C	-20°C To +90°C

<b>Bend Radius</b>
Installation Min.

3.15 in (80.0 mm)

Max. Pull Tension:	99 lbs (45 kg)
Bulk Cable Weight:	67 lbs/1000ft (100 kg/km)

Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Indoor, Outdoor, UV Resistance, Burial
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	UL 1685, FT4
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 725, Article 760, CL3, FPL, PLTC
TIA/EIA Compliance:	TIA455-82 Water Penetration Test
European Directive Compliance:	EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.4 Revision Date: 07-11-2025
----------------------	--

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.