



Product: [513945E](#)

Surveillance CCTV, RG-11 #14 BC, 95% BC Braid, PVC, Eca

Product Description

Surveillance and CCTV Cable, Coax RG11/U, Solid bare copper, gas injected polyethylene, 95% bare copper braid, PVC jacket

Technical Specifications

Product Overview

Suitable Applications:	Coaxial cable used in analogue video and CCTV communication networks designed according European Standard EN 50117-1; Operating at frequencies between 5 and 1000 MHz
------------------------	---

Construction Details

RG Type:	11
----------	----

Conductor

No. of Elements	Size	Stranding	Nom. Diameter	Material
1	14 AWG	Solid	1.63 mm	BC - Bare Copper

Insulation

Material	Nom. Insulation Diameter
PE - Polyethylene (Foam)	7.11 mm (0.280 in)

Outer Shield

Outer Shield Type	Material	Coverage
Braid	Bare Copper (BC)	95%

Outer Jacket

Material	Nom. Diameter
PVC - Polyvinyl Chloride	10.3 mm

Electrical Characteristics

Return Loss (RL)

Frequency	Min. Return Loss
5 - 30 MHz	23 dB
30 - 470 MHz	23 dB
470 - 1000 MHz	20 dB

Table Notes:	In each frequency band, 3 peak values up to 4 dB lower are allowed
--------------	--

Attenuation

Frequency	Nom. Attenuation
1 MHz	0.56 dB/100m
10 MHz	1.15 dB/100m
50 MHz	2.95 dB/100m
100 MHz	4.26 dB/100m
200 MHz	6.2 dB/100m
400 MHz	9.5 dB/100m
700 MHz	13.5 dB/100m
900 MHz	15.8 dB/100m

1000 MHz	17.1 dB/100m
Table Notes:	Max. attenuation 10% higher

Electricals

Max. Conductor DCR	Nom. Capacitance Cond-to-Shield	Nom. Characteristic Impedance	Nom. Velocity of Prop.
8.5 Ohm/km (2.6 Ohm/1000ft)	53 pF/m (16 pF/ft)	75 Ohm	84%

Mechanical Characteristics

Temperature

Operating	Installation	Storage
-30°C To +75°C	-5°C To +50°C	-30°C To +75°C

Bend Radius

Stationary Min.
101 mm (3.98 in)

Bulk Cable Weight:	119 kg/km
--------------------	-----------

Standards and Compliance

Environmental Suitability:	Indoor - Euroclass Eca
Flammability / Reaction to Fire:	IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
CENELEC Compliance:	EN 50117-1, EN 50117-9-1, EN 50290-2-20
UK Regulation Compliance:	UKCA Mark

History

Update and Revision:	Revision Number: 0.244 Revision Date: 02-03-2025
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	EAN
513945E.00305	Black	Reel	305 m	8719605007896
513945E.001000	Black	Reel	1,000 m	8719605007889

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.