



REPRESENTATIVE IMAGE

Product: [5201UE](#)

Security & Sound, 3 Conductor 16 AWG, BC, CMR

Product Description

Security & Commercial Audio Cable, Riser-CMR, 3-16 AWG stranded bare copper conductors with polypropylene insulation, PVC jacket with ripcord

Technical Specifications

Product Overview

Suitable Applications:	Addressable Fire Systems, Data Circuits, Monitor/Detection, Control Circuits, Initiating Circuits, Notification Circuits
------------------------	--

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	3	16 AWG	19x29	BC - Bare Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PO - Polyolefin	0.008 in (0.20 mm)	0.073 in (1.9 mm)	Black, Red, White

Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.017 in (0.43 mm)	0.191 in (4.85 mm)	Yes

Overall Cable Diameter (Nominal): 0.191 in (4.85 mm)

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Max. Current
Conductor(s)	4.2 Ohm/1000ft	23.5 pF/ft (77.1 pF/m)	6.25 Amps per conductor @ 25°C

Voltage

UL Voltage Rating
300 V (CMR)

Mechanical Characteristics

Temperature

UL Temperature	Operating
75°C	-20°C to +75°C

Bend Radius

Stationary Min.	Installation Min.
1.9 in (48 mm)	1.9 in (48 mm)

Max. Pull Tension:	88 lbs (40 kg)
Bulk Cable Weight:	32 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor - Riser, Indoor
Flammability / Reaction to Fire:	UL 1666 Riser, FT4, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 800, CMR
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Plenum Number:	6201UE

History

Update and Revision:	Revision Number: 0.498 Revision Date: 04-28-2023
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC/EAN	Footnote
5201UE.00305	Gray	Reel	305 m	8719605008053	
5201UE.00U305	Gray	Reel	305 m	8719605008060	
5201UE 008500	Gray	Reel	500 ft	612825157809	
5201UE 0081000	Gray	Reel	1,000 ft	612825157823	C
5201UE 008U1000	Gray	UnReel	1,000 ft	612825425687	
5201UE 008Z1000	Gray	ReelTuff Box	1,000 ft	612825157847	

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.