



Product: [5220/2C](#) 

XTRAGUARD 1, 2C #20, Str, PVC, Semi Rigid, 300 V, AWM/STYLE 2343 80C, CM 105C, VW-1, AWM/STYLE 10002 105C, AWM/STYLE 2517 105C, SUN RES, CSA CMG, CSA FT4

Product Description

XTRAGUARD 1, 2 Conductor 20 AWG (7/28) TC - Tinned Copper, PVC, Semi Rigid Insulation, Slate PVC Outer Jacket, AWM/STYLE 2343 80C, CM 105C, VW-1, AWM/STYLE 10002 105C, AWM/STYLE 2517 105C, SUN RES, CSA CMG, CSA FT4 CMG, FT4 UL FT4, VW-1; CSA FT4; EN 60332-1 Flame Behavior; EN 60332-2 Flame Behavior

Technical Specifications

Product Overview

| | |
|------------------------|--|
| Suitable Applications: | Industrial control systems, raceways, cable trays, and ducts; instrumentation and control circuits; analog and digital signals (4–20 mA, 0–10 V); PLC and DCS systems; sensors, encoders, solenoids, valves, actuators, and positioners. |
|------------------------|--|

Construction Details

Conductor

| Element | No. of Elements | Size | Stranding | Material |
|--------------|-----------------|--------|-----------|--------------------|
| Conductor(s) | 2 | 20 AWG | 7x28 | TC - Tinned Copper |

Insulation

| Element | Material | Nom. Thickness | Nom. Insulation Diameter | Color Code |
|--------------|--|--------------------|--------------------------|--------------|
| Conductor(s) | SR-PVC - Polyvinyl Chloride (Semi-Rigid) | 0.010 in (0.25 mm) | 0.058 in (1.5 mm) | Black, Brown |

Outer Jacket

| Material | Nom. Thickness | Nom. Diameter | Ripcord |
|--------------------------|-------------------|--------------------|---------|
| PVC - Polyvinyl Chloride | 0.063 in (1.6 mm) | 0.246 in (6.25 mm) | Yes |

| | |
|-----------------------------------|--------------------|
| Overall Cable Diameter (Nominal): | 0.246 in (6.25 mm) |
|-----------------------------------|--------------------|

Electrical Characteristics

Electricals

| Element | Nom. Capacitance Cond-to-Cond | Nom. Characteristic Impedance | Nom. Inductance |
|--------------|-------------------------------|-------------------------------|------------------------|
| Conductor(s) | 24.5 pF/ft (80.4 pF/m) | 73 Ohm | 0.17 µH/ft (0.56 µH/m) |

Voltage

| UL Voltage Rating |
|-------------------------------------|
| 300 V (CM, CMG, AWM 2343, AWM 2517) |

Mechanical Characteristics

Temperature

| UL Temperature | Operating |
|----------------|-----------------|
| 105°C | -35°C To +105°C |

Bend Radius

| Stationary Min. | Installation Min. |
|-----------------|-------------------|
| 2.0 in (51 mm) | 2.0 in (51 mm) |

| | |
|--------------------|----------------|
| Max. Pull Tension: | 50 lbs (23 kg) |
|--------------------|----------------|

Standards and Compliance

| | |
|----------------------------------|--|
| Environmental Suitability: | Indoor, Outdoor, Sunlight Resistance |
| Sustainability: | CA Prop 65 |
| Flammability / Reaction to Fire: | UL1685 FT4 Loading, FT4, IEC 60332-1-2, IEC 60332-2-2 |
| NEC / UL Compliance: | Article 800, CMG, CM |
| AWM Compliance: | AWM 2343AWM 2517 |
| CEC / C(UL) Compliance: | CMG |
| European Directive Compliance: | EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE) |
| UK Regulation Compliance: | UKCA Mark |
| APAC Compliance: | China RoHS II (GB/T 26572-2011) |

Product Notes

| | |
|--------|---|
| Notes: | Alpha Wire -* P/N 5220/2C 2C 20 AWG XTRAGUARD(R) 1 (UL) TYPE CM 105C SUN RES OR AWM 2343 80C 300V OR AWM 2517 105C 300V VW-1 --- LLXXXXXX CSA 105C TYPE CMG FT4 CE ROHS OIL RESISTANT (SEQ FOOTAGE) |
|--------|---|

History

| | |
|----------------------|---|
| Update and Revision: | Revision Number: 0.15 Revision Date: 06-30-2026 |
|----------------------|---|

Part Numbers

Variants

| Item # | Color | Putup Type | Length |
|---------------|-------|------------|--------|
| 5220/2C SL005 | Black | Reel | 100 ft |

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.