



Product: [5284US](#)

PTZ, #24-2pr, #16-2c, CMR, Siamese

Product Description

PTZ (Control + Power) Cable, Riser-CMR, 2-24 AWG solid bare copper pairs with polyolefin insulation, 2-16 AWG stranded bare copper conductors with PVC insulation, Siamese PVC jacket

Technical Specifications

Product Overview

Suitable Applications:	Surveillance, CCTV Camera, PTZ (Pan-Tilt-Zoom), UTP-CCTV
Patent:	This product has one or more applicable patents. More information on patents can be found at https://www.belden.com/resources/patents .

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Conductors	No. of Pairs
24	Solid	BC - Bare Copper		2
16		BC - Bare Copper	2	

Conductor Count:	6
Total Number of Pairs:	3

Insulation

Material	Nominal Diameter
PO - Polyolefin	0.035 in
PO - Polyolefin	

Color Chart

Number	Color
Cat 5e Pair1	Blue and White/Blue
Cat 5e Pair2	Orange and White/Orange
Pair1	Black & Red

Inner Shield Material

Material
No Shield
No Shield

Outer Jacket Material

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.190 x 0.408 in

Electrical Characteristics

Conductor DCR

Element	Max. Conductor DCR	Max. DCR Unbalance
Cat 5e Pair	28.5902 Ohm/1000ft	5 %
	45 Ohm/km	

Capacitance

Element
Cat 5e Pair
Pair1

Delay

Element	Max. Delay	Max. Delay Skew
Cat 5e Pair	45 ns/ft	70 ns/100m

High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. PSNEXT [dB]	Min. PSACR [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Fitted Impedance
1 MHz	2 dB/100m	62 dB	60 dB	61 dB	20 dB	100 ± 15%
4 MHz	4.1 dB/100m	53 dB	49 dB	49 dB	23 dB	100 ± 15%
8 MHz	5.8 dB/100m	48 dB	43 dB	43 dB	24.5 dB	100 ± 15%
10 MHz	6.5 dB/100m	47 dB	41 dB	41 dB	25 dB	100 ± 15%
16 MHz	8.2 dB/100m	44 dB	36 dB	37 dB	25 dB	100 ± 15%
20 MHz	9.3 dB/100m	42 dB	34 dB	35 dB	25 dB	100 ± 15%
25 MHz	10.4 dB/100m	41 dB	31 dB	33 dB	24.3 dB	100 ± 15%
31.25 MHz	11.7 dB/100m	39 dB	28 dB	31 dB	23.6 dB	100 ± 15%
62.5 MHz	17 dB/100m	35 dB	19 dB	24 dB	21.5 dB	100 ± 15%
100 MHz	22 dB/100m	32 dB	11 dB	21 dB	20.1 dB	100 ± 15%

Current

Element
Cat 5e Pair
Pair1

Voltage

UL Voltage Rating
300 VRMS

Electrical Characteristics Notes: Maximum DCR Unbalance for Pair @ 20°C: 5%

Temperature Range

Installation Temp Range:	0°C To +75°C
UL Temp Rating:	75°C
Operating Temp Range:	-20°C To +75°C
Separation Temp Range:	0°C To +75°C

Mechanical Characteristics

Bulk Cable Weight:	43 lbs/1000ft
Max. Pull Tension:	100 lbs

Standards

NEC Articles:	Article 800
NEC/(UL) Compliance:	CMR
CEC/C(UL) Compliance:	CMG
IEC Compliance:	ISO/IEC 11801, Category 5e for data pair
Third Party Performance Verification:	Category 5e

Applicable Environmental and Other Programs

Environmental Space:	Indoor - Riser
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	Yes
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Flammability, LSOH, Toxicity Testing

C(UL) Flammability:	FT4
UL Flammability:	UL1666 Riser
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	6284US

Part Number

Variants

Item #	Color	UPC
5284US 0101000	Black	612825158875
5284US 010500	Black	612825158882
5284US 0091000	White	612825158868

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

Product Notes

Notes:	Overall jacket sequentially marked.
--------	-------------------------------------

History

Update and Revision:	Revision Number: 0.262 Revision Date: 02-16-2021
----------------------	--

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.