



**Product:** [5302U1](#)

Security & Sound, #18-4c, TC, CMG-FPL-PLTC, Water-Blocked

### Product Description

Security & Sound Cable, Rated-CMG-FPL-PLTC, 4-18 AWG stranded tinned copper conductors with PVC insulation, Waterblocking tape, PVC jacket

### Technical Specifications

#### Product Overview

Suitable Applications:	Security System, Intercom/PA, Audio/Speaker, Power-Limited Controls, Wet Location, Below-Grade Duct
------------------------	---

#### Construction Details

##### Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	4	18 AWG	7x26	TC - Tinned Copper

##### Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PVC - Polyvinyl Chloride	0.017 in (0.43 mm)	0.080 in (2.0 mm)	Black, White, Red, Green

Waterblocking:	Waterblock Tape
----------------	-----------------

##### Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.042 in (1.1 mm)	0.309 in (7.85 mm)

Overall Cable Diameter (Nominal):	0.309 in (7.85 mm)
-----------------------------------	--------------------

#### Electrical Characteristics

##### Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Max. Current
Conductor(s)	5.9 Ohm/1000ft	30 pF/ft (98 pF/m)	7.2 Amps per conductor @ 25°C

##### Voltage

UL Voltage Rating
300 V (CMG, FPL, PLTC-ER)

#### Mechanical Characteristics

##### Temperature

UL Temperature	Operating
105°C	-30°C to +105°C

##### Bend Radius

Stationary Min.	Installation Min.
3.1 in (79 mm)	3.1 in (79 mm)

Max. Pull Tension:	89 lbs (40 kg)
Bulk Cable Weight:	40 lbs/1000ft

## Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Indoor, Outdoor, Sunlight Resistance
Flammability / Reaction to Fire:	UL 1685 FT4 Loading, FT4, IEEE 1202
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 725, Article 760, Article 800
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark

## History

Update and Revision:	Revision Number: 0.427 Revision Date: 02-03-2025
----------------------	--

## Part Numbers

### Variants

Item #	Color	UPC	Footnote
5302U1 0101000	Black	612825159797	C

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.