



**Product:** [5339Q5](#)

Surveillance CATV MATV, RG-6 #18 BC, Quad Shield, CM

**Product Description**

Surveillance, CATV & MATV Cable, RG6, Rated-CM, 18 AWG solid bare copper, foam polyolefin core, quad shield-Duofoil® + 60% aluminum braid + Duofoil® + 40% aluminum braid, PVC jacket

**Technical Specifications**

**Product Overview**

Suitable Applications:	CATV, MATV
------------------------	------------

**Physical Characteristics (Overall)**

**Conductor**

AWG	Stranding	Material	Nominal Diameter	No. of Coax
18	Solid	BC - Bare Copper	0.040 in	1

Conductor Count:	1
------------------	---

**Insulation**

Layer	Material	Nominal Diameter
1	PE - Polyethylene (Foam)	0.180 in

Table Notes:	Gas Injected
--------------	--------------

**Color Chart 2**

Number
1

**Outer Shield Material**

Type	Layer	Material	Material Trade Name	Coverage [%]
Tape	1	Tri-Laminate (Alum+Poly+Alum)	Duofoil®	100%
Braid	2	Aluminum		60%
Tape	3	Tri-Laminate (Alum+Poly+Alum)	Duofoil®	100%
Braid	4	Aluminum		40%

**Outer Jacket Material**

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.298 in

**Electrical Characteristics**

**Conductor DCR**

Nominal Conductor DCR	Nominal Conductor DCR Conductor Resistance	Nominal Outer Shield DCR	Outer Conductor DCR
6.5 Ohm/1000ft	6.5 Ohm/1000ft	7 Ohm/1000ft	7.0 Ohm/1000ft

**Capacitance**

Nom. Capacitance Conductor to Shield
16.2 pF/ft

## Inductance

### Nominal Inductance

0.097 µH/ft

## Impedance

### Nominal Characteristic Impedance

75 Ohm

## Delay

### Max. Delay Skew | Nominal Delay | Nominal Velocity of Propagation (VP) [%]

83 ns/100m | 1.24 ns/ft | 82%

## High Freq

### Frequency [MHz] | Max. Insertion Loss (Attenuation)

5 MHz	0.81 dB/100ft
55 MHz	1.6 dB/100ft
211 MHz	3.08 dB/100ft
270 MHz	3.5 dB/100ft
300 MHz	3.7 dB/100ft
330 MHz	3.89 dB/100ft
400 MHz	4.3 dB/100ft
450 MHz	4.58 dB/100ft
550 MHz	5.09 dB/100ft
750 MHz	6 dB/100ft
870 MHz	6.5 dB/100ft
1000 MHz	7 dB/100ft

## Voltage

### Non-UL Voltage Rating

300 V RMS

## Temperature Range

UL Temp Rating:	75°C
Operating Temp Range:	-40°C To +80°C

## Mechanical Characteristics

Bulk Cable Weight:	35 lbs/1000ft
Max. Pull Tension:	76 lbs
Min Bend Radius/Minor Axis:	3 in

## Standards

NEC/(UL) Compliance:	CATV, CM
CEC/C(UL) Compliance:	CM
CPR Euroclass:	Eca
RG Type:	6/U Type
Series Type:	6

## Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
MII Order #39 (China RoHS):	Yes

## Suitability

Suitability - Aerial:	Yes - When supported by messenger wire
Suitability - Burial:	No
Suitability - Hazardous Locations:	No

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes

## Flammability, LSOH, Toxicity Testing

C(UL) Flammability:	FT1
UL Flammability:	UL1685 UL Loading
IEC Flammability:	IEC 60332-1-2

## Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	6339Q8

## Part Number

### Variants

Item #	Color	Putup Type	Length	UPC
5339Q5 0101000	Black	Reel	1,000 ft	612825160977
5339Q5 010U1000	Black	UnReel	1,000 ft	612825160960
5339Q5 009U500	White	UnReel	500 ft	612825160946
5339Q5 0091000	White	Reel	1,000 ft	612825160953
5339Q5 009U1000	White	UnReel	1,000 ft	612825160939

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

## Product Notes

Notes:	Print legend includes sequential footage marks.
--------	---

## History

Update and Revision:	Revision Number: 0.300 Revision Date: 09-30-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.