



Product: [5341FE](#)

Security & Sound, #18-2pr, BC, Shielded, CMR

### Product Description

Security & Sound Cable, Riser-CMR, 2-18 AWG stranded bare copper pairs with polypropylene insulation, Beldfoil® shield and PVC jacket with ripcord

### Technical Specifications

#### Product Overview

Suitable Applications:	Security System, Intercom/PA, Audio/Speaker, Power-Limited Controls, Noisy Environment
------------------------	--

#### Construction Details

##### Conductor

Element	No. of Elements	Size	Stranding	Material
Pair(s)	2	18 AWG	7x26	BC - Bare Copper

##### Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Pair(s)	PP - Polypropylene	0.007 in (0.18 mm)	0.062 in (1.6 mm)	Black & Red, Black & White

##### Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	24 AWG (7x32) TC

##### Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.017 in (0.43 mm)	0.250 in (6.35 mm)	Yes

Overall Cable Diameter (Nominal):	0.250 in (6.35 mm)
-----------------------------------	--------------------

#### Electrical Characteristics

##### Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Max. Current
Pair(s)	6.55 Ohm/1000ft	29 pF/ft (95 pF/m)	52.25 pF/ft (171.4 pF/m)	7.2 Amps per conductor @ 25°C

##### Voltage

UL Voltage Rating
300 V (CMR)

#### Mechanical Characteristics

##### Temperature

UL Temperature	Operating
75°C	-20°C to +75°C

##### Bend Radius

Stationary Min.	Installation Min.
2.5 in (64 mm)	2.5 in (64 mm)

Max. Pull Tension:	104 lbs (47.2 kg)
Bulk Cable Weight:	33 lbs/1000ft

## Standards and Compliance

Environmental Suitability:	Indoor - Riser, Indoor
Flammability / Reaction to Fire:	UL 1666 Riser, FT4, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 800, CMR
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU CE Mark
UK Regulation Compliance:	UKCA Mark

## History

Update and Revision:	Revision Number: 0.459 Revision Date: 12-22-2023
----------------------	--

## Part Numbers

### Variants

Item #	Color	Putup Type	Length	UPC/EAN	Footnote
5341FE.00305	Chrome	Reel	305 m	8719605008435	
5341FE.00800	Chrome	Reel	800 m	8719605184733	
5341FE 0081000	Gray			612825161189	C
5341FE 008500	Gray			612825161196	C
5341FE 008U1000	Gray			612825161172	
5341FE 0081200	Gray			612825352693	
5341FE 0081200	Gray			612825352693	
5341FE 0081500	Gray			612825352709	
5341FE 0081500	Gray			612825352709	

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.