

Product: [50098TPE](#) 

2C2.5mm², Cu. Cond., PVC Ins, TPE Jkt As-Interface Bus Flat Cable.



Product Description

2 Cores 2.5 mm², Stranded Annealed Tinned Copper Conductors, PVC insulated & Overall TPE Jacket As- Interface Bus Flat cable.

Technical Specifications

Product Overview

Suitable Applications:	For applications up to and including 300V.
------------------------	--

Construction Details

Conductor

Element	No. of Elements	Size	Material
Conductor(s)	2	2.5 mm ²	TC - Tinned Copper (High Conductivity)

Insulation

Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
PVC - Polyvinyl Chloride	0.25 mm (0.0098 in)	2.5 mm (0.098 in)	Brown, Blue

Conductor Spacing Center-Center:	3.6 ± 0.2 mm
----------------------------------	--------------

Outer Jacket

Material	Nom. Thickness	Nom. Thickness Flat Section	Nom. Width
TPE - Thermoplastic Elastomer	0.55 mm (0.022 in)		6.5 mm
		4.0 mm	10 mm

Electrical Characteristics

Electricals

Max. Conductor DCR	Nom. Capacitance Cond-to-Cond
8.21 Ohms @ 20 Deg C	80 pF/ft (260 pF/m)

Voltage

UL Voltage Rating	Breakdown Voltage
300 V	2000 V

Mechanical Characteristics

Temperature

Operating
-30°C to +105°C

Standards and Compliance

Flammability / Reaction to Fire:	FT4
AWM Compliance:	AWM I/II A/B
CEC / C(UL) Compliance:	C22.2 No.210.2
European Directive Compliance:	EU Directive 2011/65/EU (RoHS 2)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Other Standard Compliance(s):	UL 758
-------------------------------	--------

Product Notes

Notes:	UL 13, EN 50295, IEC 62026-2
--------	------------------------------

History

Update and Revision:	Revision Number: 0.15 Revision Date: 10-02-2026
----------------------	---

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.