



**Product:** [5682](#) 

XTRAGUARD 1, 2C #26, Str, PVC, Semi Rigid, 300 V, AWM/STYLE 10002 105C, AWM/STYLE 2464 80C, CM 105C, VW-1, AWM/STYLE 2517 105C, SUN RES, CSA CMG, CSA FT4

## Product Description

XTRAGUARD 1, 2 Conductor 26 AWG (7/34) TC - Tinned Copper, PVC, Semi Rigid Insulation, Overall Aluminum/Polyester Shield, Slate PVC Outer Jacket, AWM/STYLE 10002 105C, AWM/STYLE 2464 80C, CM 105C, VW-1, AWM/STYLE 2517 105C, SUN RES, CSA CMG, CSA FT4 CMG, FT4 UL FT4, VW-1; CSA FT4; EN 60332-1 Flame Behavior; EN 60332-2 Flame Behavior

## Technical Specifications

### Product Overview

Suitable Applications:	Data, communication, audio, and low-level signal transmission; industrial networking, serial communication, control panels, automation equipment, and instrumentation systems.
------------------------	--

### Construction Details

#### Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	2	26 AWG	7x34	TC - Tinned Copper

#### Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	SR-PVC - Polyvinyl Chloride (Semi-Rigid)	0.010 in (0.25 mm)	0.039 in (0.99 mm)	Black, Brown

#### Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Braid	Bi-Laminate (Alum+Poly)	100%	26 AWG (7x34) TC
Braid	Tinned Copper (TC)	70%	

#### Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.032 in (0.81 mm)	0.174 in (4.42 mm)	Yes

Overall Cable Diameter (Nominal):	0.174 in (4.42 mm)
-----------------------------------	--------------------

### Electrical Characteristics

#### Electricals

Element	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedence	Nom. Inductance
Conductor(s)	30 pF/ft (98 pF/m)	54 pF/ft (180 pF/m)	63 Ohm	0.2 µH/ft (0.66 µH/m)

Nom Outer Shield DCR:	73 Ohm/1000ft (240 Ohm/km)
-----------------------	----------------------------

#### Voltage

UL Voltage Rating
300 V (CM, CMG, AWM 2464, AWM 2517)

### Mechanical Characteristics

#### Temperature

UL Temperature	Operating
105°C	-35°C To +105°C

## Bend Radius

### Stationary Min.

1.7 in (43 mm)

Max. Pull Tension: 28 lbs (13 kg)

## Standards and Compliance

Environmental Suitability:	Indoor, Outdoor, Sunlight Resistance
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	UL1685 FT4 Loading, FT4, IEC 60332-1-2, IEC 60332-2-2
NEC / UL Compliance:	Article 800, CMG, CM
AWM Compliance:	AWM 2464AWM 2517
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

## Product Notes

Notes: Alpha Wire -\* P/N 5682 2C 26 AWG XTRAGUARD(R) 1 SHIELDED (UL) TYPE CM 105C SUN RES OR AWM 2464 80C 300V OR AWM 2517 105C 300V VW-1 --- LLXXXXX CSA 105C TYPE CMG FT4 CE ROHS OIL RESISTANT (SEQ FOOTAGE)

## History

Update and Revision: Revision Number: 0.122 Revision Date: 06-30-2026

## Part Numbers

### Variants

Item #	Color	Putup Type	Length
5682 SL005	Black	Reel	100 ft
5682 SL002	Black	Reel	500 ft
5682 SL001	Black	Reel	1,000 ft

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.