


**Product:** [513945](#) 



Surveillance CCTV, RG-11 #14 BC, 95% BC Braid, CM

**Product Description**

Surveillance & CCTV Cable, RG11, Rated-CM, 14 AWG solid bare copper, foam polyolefin core, 95% bare copper braid, PVC jacket

**Technical Specifications**

**Product Overview**

Suitable Applications:	Surveillance, CCTV Camera
------------------------	---------------------------

**Physical Characteristics (Overall)**

**Conductor**

AWG	Stranding	Material	Nominal Diameter	No. of Coax
14	Solid	BC - Bare Copper	0.064 in	1

**Insulation**

Material	Nominal Diameter
PE - Polyethylene (Foam)	0.28 in

Table Notes:	Gas Injected
--------------	--------------

**Outer Shield Material**

Type	Material	Coverage [%]
Braid	Bare Copper (BC)	95%

**Outer Jacket Material**

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.405 in
	0.463 in

Weight:	0.46 lbs
---------	----------

**Electrical Characteristics**

**Conductor DCR**

Nominal Conductor DCR	Nominal Conductor DCR	Conductor Resistance	Nominal Outer Shield DCR	Outer Conductor DCR
2.6 Ohm/1000ft	2.6 Ohm/1000ft		1.2 Ohm/1000ft	1.2 Ohm/1000ft

**Capacitance**

Nom. Capacitance Conductor to Shield
16.1 pF/ft

**Inductance**

Nominal Inductance
0.106 $\mu$ H/ft

**Impedance**

Nominal Characteristic Impedance
75 Ohm

#### High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
1 MHz	0.17 dB/100ft
10 MHz	0.35 dB/100ft
50 MHz	0.9 dB/100ft
100 MHz	1.3 dB/100ft
200 MHz	1.9 dB/100ft
400 MHz	2.9 dB/100ft
700 MHz	4.1 dB/100ft
900 MHz	4.8 dB/100ft
1000 MHz	5.2 dB/100ft

#### Delay

Max. Delay Skew	Nominal Delay	Nominal Velocity of Propagation (VP) [%]
84 ns/100m	1.21 ns/ft	84%

#### Voltage

Non-UL Voltage Rating	UL Voltage Rating
600 V RMS	300 V RMS

#### Temperature Range

UL Temp Rating:	75°C
Operating Temp Range:	-30°C To +75°C

#### Mechanical Characteristics

Bulk Cable Weight:	82 lbs/1000ft
Max. Pull Tension:	144 lbs
Min. Bend Radius/Minor Axis:	4 in

#### Standards

NEC Articles:	Article 800
NEC/(UL) Compliance:	CM
CEC/C(UL) Compliance:	CM
CPR Euroclass:	Eca
RG Type:	11
Series Type:	11

#### Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	Yes
EU CE Mark:	Yes
MII Order #39 (China RoHS):	Yes

#### Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes - Black only

#### Flammability, LS0H, Toxicity Testing

C(UL) Flammability:	FT1
IEC Flammability:	IEC 60332-1-2
UL voltage rating:	300 V RMS

#### Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	613948

## Part Number

---

### Variants

Item #	Color	Put-Up Type	Length	UPC/EAN
513945.00305	Black	Reel	305 m	8719605007858
513945.00500	Black	Reel	500 m	8719605007865
513945 0101000	Black	Reel	1,000 ft	612825157137

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

### History

---

Update and Revision:	Revision Number: 0.404 Revision Date: 09-10-2021
----------------------	--

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.