



Product: [5302FE](#)

Security & Sound, #18-4c, BC, Shielded, CMR

Product Description

Security & Sound Cable, Riser-CMR, 4-18 AWG stranded bare copper conductors with polypropylene insulation, Beldfoil® shield and PVC jacket with ripcord

Technical Specifications

Product Overview

| | |
|------------------------|--|
| Suitable Applications: | Security System, Intercom/PA, Audio/Speaker, Power-Limited Controls, Noisy Environment |
|------------------------|--|

Construction Details

Conductor

| Element | Number of Element | Size | Stranding | Material |
|--------------|-------------------|--------|-----------|------------------|
| Conductor(s) | 4 | 18 AWG | 7x26 | BC - Bare Copper |

Insulation

| Element | Material | Nom. Thickness | Nom. Insulation Diameter | Color Code |
|--------------|-----------------|--------------------|--------------------------|--------------------------|
| Conductor(s) | PO - Polyolefin | 0.009 in (0.23 mm) | 0.062 in (1.6 mm) | Black, Red, White, Green |

Outer Shield

| Shield Type | Material | Coverage | Drainwire Type |
|-------------|-------------------------|----------|------------------|
| Tape | Bi-Laminate (Alum+Poly) | 100% | 24 AWG (7x32) TC |

Outer Jacket

| Material | Nom. Thickness | Nom. Diameter | Ripcord |
|--------------------------|--------------------|--------------------|---------|
| PVC - Polyvinyl Chloride | 0.017 in (0.43 mm) | 0.188 in (4.78 mm) | Yes |

| | |
|-----------------------------------|--------------------|
| Overall Cable Diameter (Nominal): | 0.188 in (4.78 mm) |
|-----------------------------------|--------------------|

Electrical Characteristics

Electricals

| Element | Nom. Conductor DCR | Nom. Capacitance Cond-to-Cond | Nom. Capacitance Cond-to-Other (Conds + Shield) | Max. Current |
|--------------|--------------------|-------------------------------|---|-----------------------------|
| Conductor(s) | 6.5 Ohm/1000ft | 27 pF/ft (89 pF/m) | 48.5 pF/ft (159 pF/m) | 4 Amps per conductor @ 25°C |

Voltage

| |
|--------------------------|
| UL Voltage Rating |
| 300 V (CMR) |

Mechanical Characteristics

Temperature

| UL Temperature | Operating |
|----------------|----------------|
| 75°C | -20°C to +75°C |

Bend Radius

| Stationary Min. | Installation Min. |
|-----------------|-------------------|
| 1.9 in (48 mm) | 1.9 in (48 mm) |

| | |
|--------------------|-------------------|
| Max. Pull Tension: | 104 lbs (47.2 kg) |
| Bulk Cable Weight: | 31 lbs/1000ft |

Standards and Compliance

| | |
|----------------------------------|--|
| Environmental Suitability: | Indoor - Riser, Indoor |
| Flammability / Reaction to Fire: | UL 1666 Riser, FT4, IEC 60332-1-2 |
| CPR Compliance: | CPR Euroclass: Eca |
| NEC / UL Compliance: | Article 800, CMR |
| CEC / C(UL) Compliance: | CMG |
| European Directive Compliance: | EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE) |
| UK Regulation Compliance: | UKCA Mark |
| APAC Compliance: | China RoHS II (GB/T 26572-2011) |
| Plenum Number: | 6302FE |

History

| | |
|----------------------|--|
| Update and Revision: | Revision Number: 0.450 Revision Date: 01-20-2023 |
|----------------------|--|

Part Numbers

Variants

| Item # | Color | Putup Type | Length | UPC/EAN |
|-----------------|--------|------------|--------|---------------|
| 5302FE.00152 | Chrome | Reel | 152 m | 8719605008220 |
| 5302FE.00305 | Chrome | Reel | 305 m | 8719605008237 |
| 5302FE.00U305 | Chrome | Reel | 305 m | 8719605008244 |
| 5302FE 0081000 | Gray | | | 612825336846 |
| 5302FE 008500 | Gray | | | 612825159551 |
| 5302FE 008C250 | Gray | | | |
| 5302FE 008U1000 | Gray | | | 612825159537 |
| 5302FE 008U500 | Gray | | | 612825159544 |

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.