



**Product:** [5399B5](#)

Surveillance CATV MATV, RG-6 #18 BC, Duobond+60% AL Braid, CM

**Product Description**

Surveillance, CATV & MATV Cable, RG6, Rated-CM & CL2, 18 AWG solid bare copper, foam polyolefin core, Duobond® + 60% aluminum braid, PVC jacket

**Technical Specifications**

**Product Overview**

Suitable Applications:	CATV, MATV, Schlage Systems
------------------------	-----------------------------

**Physical Characteristics (Overall)**

**Conductor**

AWG	Stranding	Material	Nominal Diameter	No. of Coax
18	Solid	BC - Bare Copper	0.040 in	1

Conductor Count:	1
------------------	---

**Insulation**

Material	Nominal Diameter
PE - Polyethylene (Foam)	0.180 in

**Outer Shield**

Type	Layer	Material	Material Trade Name	Coverage [%]
Tape	1	Tri-Laminate (Alum+Poly+Alum)	Duofoil®	100%
Braid	2	Aluminum		60%

Table Notes:	Tape is bonded to dielectric
--------------	------------------------------

**Outer Jacket**

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.270 in

**Electrical Characteristics**

**Conductor DCR**

Nominal Conductor DCR	Nominal Conductor DCR Conductor Resistance	Nominal Outer Shield DCR	Outer Conductor DCR
6.5 Ohm/1000ft	6.5 Ohm/1000ft	9 Ohm/1000ft	9.0 Ohm/1000ft

**Capacitance**

Nom. Capacitance Conductor to Shield
16.3 pF/ft

**Inductance**

Nominal Inductance
0.097 µH/ft

**Impedance**

Nominal Characteristic Impedance
75 Ohm

## Return Loss (RL)

Frequency [MHz]	Min. Structural Return Loss (SRL)
5-50 MHz	23 dB

## Delay

Max. Delay Skew	Nominal Delay	Nominal Velocity of Propagation (VP) [%]
83 ns/100m	1.22 ns/ft	83%

## High Frequency

Frequency [MHz]	Max. Insertion Loss (Attenuation)
4 MHz	0.6 dB/100ft
30 MHz	1.33 dB/100ft
211 MHz	3.08 dB/100ft
270 MHz	3.5 dB/100ft
300 MHz	3.7 dB/100ft
330 MHz	3.89 dB/100ft
400 MHz	4.3 dB/100ft
450 MHz	4.58 dB/100ft
550 MHz	5.09 dB/100ft
750 MHz	6 dB/100ft
870 MHz	6.5 dB/100ft
1000 MHz	7 dB/100ft

## Voltage

UL Voltage Rating
300 V RMS

## Temperature Range

UL Temp Rating:	75°C
Operating Temperature Range:	-40°C To +80°C

## Mechanical Characteristics

Bulk Cable Weight:	27 lbs/1000ft
Max. Pull Tension:	50 lbs
Min. Bend Radius/Minor Axis:	2.7 in

## Standards

NEC/(UL) Compliance:	CL2, CM
CEC/C(UL) Compliance:	CM
RG Type:	6

## Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	Yes
MII Order #39 (China RoHS):	Yes

## Suitability

Suitability - Aerial:	Yes - When supported by messenger wire
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes

## Flammability, LS0H, Toxicity Testing

C(UL) Flammability:	FT1
UL Flammability:	UL1685 UL Loading

UL voltage rating:	350 V RMS
--------------------	-----------

### Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

### Related Part Numbers

#### Variants

Item #	Color	Put-Up Type	Length	UPC
5399B5 010U1000	Black	UnReel	1,000 ft	612825161837

### Product Notes

Notes:	Print legend includes sequential footage marks.
--------	-------------------------------------------------

### History

Update and Revision:	Revision Number: 0.364 Revision Date: 04-08-2022
----------------------	--------------------------------------------------

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.