Belden



Product: 6075

Teck90 600V, 3+G C #14+14 Str BC, XLPE Ins M4, PVC Jkt, SIA Armor, Blk PVC Jkt, CSA HL SUN RES -40C

Product Description

Teck90 600V, 3+G Conductor 14+14AWG (7x22H) Bare Copper, XLPE Insulation M4 Color Code, PVC Inner Jacket, Steel Interlock Armor, Black PVC Outer Jacket, CSA HL SUN RES -40C

Technical Specifications

Product Overview

Suitable Applications:	CEC Power and Control Applications

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	3	14 AWG	7x22	BC - Bare Copper
Ground Wire	1	14 AWG	7x22	BC - Bare Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	XLP, XLPO, XLPE (Thermoset)	0.030 in (0.76 mm)	0.132 in (3.35 mm)	Black, Red, Blue
Ground Wire	No Insulation			

Outer Shield

Material
No Shield

Inner Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord	Color
PVC - Polyvinyl Chloride	0.047 in (1.2 mm)	0.378 in (9.60 mm)	Yes	Black

Armor

Armor Type & Material	Armor Thickness	Diameter Over Armor
SIA - Steel Interlock Armor	0.025 in (0.64 mm)	0.598 in (15.2 mm)

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.048 in (1.2 mm)	0.699 in

Overall Cable Diameter (Nominal):	0.699 in

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Max. Current
Conductor(s)	2.67 Ohm/1000ft	25 Amps per Conductor at 30ºC
Ground Wire	2.67 Ohm/1000ft (8.76 Ohm/km)	

Voltage

Voltage Rating

600 V (TECK 90)

Mechanical Characteristics

Temperature

UL Temperature	Operating
90°C	-40°C To +90°C

Bend Radius

Stationary Min.	Installation Min.
5.592 in (142.0 mm)	5.592 in

Max. Pull Tension:	418.4 lbs (189.8 kg)
Bulk Cable Weight:	358 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor, Outdoor, Sunlight Resistance, UV Resistance
CEC / C(UL) Compliance:	TECK 90, HL

History

Update and Revision:	Revision Number: 0.55 Revision Date: 10-07-2026

Part Numbers

Variants

Item #	Putup Type	UPC
6075 01010000	Reel	612825339366
6075 0105000	Reel	612825339373
6075 0101968	Reel	

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.