



**Product:** [5447](#) 

XTRAGUARD 1, 7C #14, Str, PVC, 600 V, AWM/STYLE 2501 105C, VW-1, AWM/STYLE 1015 105C, MTW 90C, MTW 90C, AWM/STYLE 20811 105C, CSA C(RU) AWM I/II A/B, CSA FT4, CSA TEW

## Product Description

XTRAGUARD 1, 7 Conductor 14 AWG (41/30) TC - Tinned Copper, PVC Insulation, Slate PVC Outer Jacket, AWM/STYLE 2501 105C, VW-1, AWM/STYLE 1015 105C, MTW 90C, MTW 90C, AWM/STYLE 20811 105C, CSA C(RU) AWM I/II A/B, CSA FT4, CSA TEW C(RU) AWM I/II A/B, FT4, TEW UL FT4, VW-1; CSA FT4; EN 60332-1 Flame Behavior; EN 60332-2 Flame Behavior

## Technical Specifications

### Product Overview

Suitable Applications:	Data, communication, audio, and low-level signal transmission; industrial networking, serial communication, control panels, automation equipment, and instrumentation systems.
------------------------	--

### Construction Details

#### Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	7	14 AWG	41x30	TC - Tinned Copper

#### Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PVC - Polyvinyl Chloride	0.032 in (0.81 mm)	0.137 in (3.48 mm)	Black, Brown, Red, Orange, Yellow, Green, Blue

#### Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.063 in (1.6 mm)	0.543 in (13.8 mm)	Yes

Overall Cable Diameter (Nominal): 0.543 in (13.8 mm)

### Electrical Characteristics

#### Electricals

Element	Nom. Capacitance Cond-to-Cond	Nom. Inductance
Conductor(s)	27 pF/ft (89 pF/m)	0.19 μH/ft (0.62 μH/m)

#### Voltage

UL Voltage Rating	Voltage Rating
600 V (MTW, AWM 20811, AWM 2501)	600 V (CSA AWM)

### Mechanical Characteristics

#### Temperature

UL Temperature	Operating
105°C	-30°C To +105°C

#### Bend Radius

Stationary Min.
5.4 in (140 mm)

Max. Pull Tension: 26 lbs (12 kg)

### Standards and Compliance

Environmental Suitability:	Indoor, Outdoor
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	UL1685 FT4 Loading, FT4, IEC 60332-1-2, IEC 60332-2-2
NEC / UL Compliance:	MTW
AWM Compliance:	AWM 2501AWM 20811, AWM I/II A/B
European Directive Compliance:	EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

## Product Notes

Notes:	Alpha Wire -* P/N 5447 7C 14 AWG XTRAGUARD(R) 1 (UL) MTW 600V OR AWM 2501 105C 600V OR AWM 20811 105C 600V VW-1 OR CRU AWM I/II A/B 105C 600V FT4 CE ROHS SUNLIGHT RESISTANT OIL RESISTANT (SEQ FOOTAGE)
--------	--

## History

Update and Revision:	Revision Number: 0.18 Revision Date: 06-30-2026
----------------------	---

## Part Numbers

### Variants

Item #	Color	Putup Type	Length
5447 SL001	Black	Reel	1,000 ft

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.