



Product: [5541PT](#)

Thermostat & Control, #22-2pr, TC, Individ. Foil, CMR

Product Description

Thermostat & Control Cable, Riser-CMR, 2-22 AWG stranded tinned copper pairs with foam polyolefin insulation, Individually Beldfoil® shielded and PVC jacket

Technical Specifications

Product Overview

Suitable Applications:	Thermostat, Control, Noisy Environment
------------------------	--

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
22	7x30	TC - Tinned Copper	2

Conductor Count:	4
------------------	---

Insulation

Material	Material Trade Name
PE - Polyethylene (Foam)	Datalene®

Color Chart

Number	Color
1	Black & White
2	Green & Red

Inner Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	100%	TC - Tinned copper	22	7x30

Outer Jacket Material

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.202 in

Electrical Characteristics

Conductor DCR

Individual Pair Nominal Shield DCR	Nominal Conductor DCR
12.7 Ohm/1000ft	14.5 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor
16.9 pF/ft

Inductance

Nominal Inductance
0.21 µH/ft

Delay

Max. Delay Skew	Nominal Velocity of Propagation (VP) [%]
78 ns/100m	78%

High Freq

Max./Min. Input Impedance (unFitted)
100 Ohm

Current

Max. Recommended Current [A]
8.1 Amps per Conductor at 25°C

Voltage

UL Voltage Rating
300 V RMS

Temperature Range

UL Temp Rating:	75°C
Operating Temp Range:	-20°C To +75°C

Mechanical Characteristics

Bulk Cable Weight:	23.3 lbs/1000ft
Max. Pull Tension:	54 lbs
Min. Bend Radius/Minor Axis:	2 in

Standards

NEC/(UL) Compliance:	CMR
CEC/C(UL) Compliance:	CMG

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
MII Order #39 (China RoHS):	Yes

Flammability, LSOH, Toxicity Testing

C(UL) Flammability:	FT4
UL Flammability:	UL1666 Riser
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	6541PT

Part Number

Variants

Item #	Color	UPC
5541PT 0011000	Brown	612825164265

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

History

Update and Revision:	Revision Number: 0.319 Revision Date: 08-27-2021
----------------------	--

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.