




**Product:** [5543UE](#) 

Security & Sound, #22-4pr, BC, CMR

## Product Description

Security & Sound Cable, Riser-CMR, 4-22 AWG stranded bare copper pairs with polypropylene insulation, PVC jacket with ripcord

## Technical Specifications

### Product Overview

Suitable Applications:	Security System, Intercom/PA, Audio/Speaker, Power-Limited Controls
------------------------	---

### Physical Characteristics (Overall)

#### Conductor

AWG	Stranding	Material	No. of Pairs
22	7x30	BC - Bare Copper	4

Conductor Count:	8
------------------	---

#### Insulation

Material	Nominal Wall Thickness
PP - Polypropylene	0.007 in

#### Color Chart

Number	Color
1	Black & Red
2	Black & White
3	Black & Green
4	Black & Blue

#### Outer Shield Material

Material
No Shield

#### Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness	Ripcord
PVC - Polyvinyl Chloride	0.218 in	0.018 in	Yes

### Electrical Characteristics

#### Conductor DCR

Nominal Conductor DCR
16.3 Ohm/1000ft

#### Capacitance

Nom. Capacitance Conductor to Conductor
24.11 pF/ft

#### Current

Max. Recommended Current [A]
2 Amps per Conductor at 20°C

## Voltage

<b>UL Voltage Rating</b>
300 V RMS

## Temperature Range

Operating Temp Range:	-20°C To +75°C
-----------------------	----------------

## Mechanical Characteristics

Bulk Cable Weight:	29.1 lbs/1000ft
Max. Pull Tension:	72.8 lbs
Min Bend Radius/Minor Axis:	2.2 in

## Standards

NEC/(UL) Compliance:	CMR
CEC/C(UL) Compliance:	CMG

## Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
MII Order #39 (China RoHS):	Yes

## Flammability, LS0H, Toxicity Testing

CSA Flammability:	FT4
UL voltage rating:	300 V RMS

## Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	6543UE

## Part Number

### Variants

Item #	Color	UPC
5543UE 0081000	Gray	612825164395
5543UE 008U1000	Gray	612825164388

## History

Update and Revision:	Revision Number: 0.216 Revision Date: 02-16-2021
----------------------	--

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.