



Product: [61P1604](#) 

Inst PVC/PVC, 4 Pr #16 Str BC, PVC-NYL Ins E1, OS, Blk PVC Jkt, TC-ER
NPLF 90C Dry 75C Wet

Product Description

UL Instrumentation, 4 Pair 16AWG (7x24) Bare Copper, PVC-NYL Insulation E1 Color Code, Overall Beldfoil® Shield, Black PVC Outer Jacket, TC-ER NPLF 90C Dry 75C Wet SUN RES DIR BUR

Technical Specifications

Physical Characteristics (Overall)

Conductor

Element	AWG	Stranding	Material	Nominal Diameter	No. of Pairs
Pair(s)	16	7x24	BC - Bare Copper	0.0571 in	4

Total Number of Pairs:	4
------------------------	---

Insulation

Material	Nominal Diameter	Nominal Wall Thickness
PVC/Nylon - Polyvinyl Chloride + Nylon	0.088 in	0.021 in

Color Chart

Color
Black & White and Numbered

Outer Jacket

Material	Nominal Diameter	Nominal Wall Thickness
PVC/Nylon - Polyvinyl Chloride + Nylon	0.551 in	0.063 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR
4.45 Ohm/1000ft	1.47 Ohm/1000ft

Current

Max. Recommended Current [A]
4.34 Amps per Conductor at 25°C

Voltage

UL Description	UL Voltage Rating
	600 V
NPLF	150 V

Temperature Range

UL Temperature Rating:	75°C Wet, 90°C Dry
Operating Temperature Range:	-30°C To +90°C

Mechanical Characteristics

UV Resistance:	Yes
Bulk Cable Weight:	164 lbs/1000ft

Maximum Recommended Pulling Tension:	285.6 lbs
--------------------------------------	-----------

Standards

NEC/(UL) Compliance:	TC-ER, NPLF
----------------------	-------------

Suitability

Suitability - Burial:	Yes
Suitability - Sunlight Resistance:	Yes

Flammability, LSOH, Toxicity Testing

CSA/C(UL) Flammability:	FT4
IEEE Flammability:	IEEE 1202
UL voltage rating:	600 V RMS (Type TC)

Related Part Numbers

Variants

Item #	UPC
61P1604 0105000	612825359814

History

Update and Revision:	Revision Number: 0.91 Revision Date: 08-07-2026
----------------------	---

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.