



Product: [5e LAN Category 5e CMP](#)

Category 5e Cable, 4 Pair, U/UTP, CMP

Product Description

Category 5e Premise Horizontal Cable (200MHz), 4 Pair, 24 AWG Solid Bare Copper Conductors, U/UTP, Plenum-CMP, Flamarrest® PVC-LS Jacket

Technical Specifications

Product Overview

Suitable Applications:	Premise Horizontal Cable, Ethernet 1000BASE-T, Ethernet 100BASE-TX, Ethernet 10BASE-T, PoE++, PoE+, PoE
Patent:	This product has one or more applicable patents. More information on patents can be found at https://www.belden.com/patents .

Product Life Cycle

Life Cycle:	Active - Product is available
-------------	-------------------------------

Construction Details

Conductor

Size	Stranding	Material	No. of Pairs
24 AWG	Solid	BC - Bare Copper	4

Insulation

Material	Color Code
PO+FEP - Polyolefin + Fluorinated Ethylene Propylene	White/Blue Stripe & Blue, White/Orange Stripe & Orange, White/Green Stripe & Green, White/Brown Stripe & Brown

Outer Jacket

Material	Material Trade Name	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	Flamarrest®	0.190 in (4.83 mm)	Yes

Overall Cable Diameter (Nominal):	0.190 in (4.83 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Max. Conductor DCR	Max. Capacitance Unbalance
93.8 Ohm/km (28.6 Ohm/1000ft)	330 pF/100m

Delay

Frequency	Max. Delay	Max. Delay Skew	Nom. Velocity of Prop.
100 MHz	537.6 ns/100m	45 ns/100m	72%

High Frequency

Frequency [MHz]	Max. Insertion Loss (Attenuation) [dB/100m]	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted) [Ohm]	Max./Min. Fitted Impedance [Ohm]
1	2.0	65.3	62.3	63.3	60.3	63.8	60.8	20.0	100 ± 15	100 ± 15
4	4.1	56.3	53.3	52.2	49.2	51.8	48.8	23.0	100 ± 15	100 ± 15
8	5.8	51.8	48.8	46.0	43.0	45.7	42.7	24.5	100 ± 15	100 ± 15
10	6.5	50.3	47.3	43.8	40.8	43.8	40.8	25.0	100 ± 15	100 ± 15
16	8.2	47.2	44.2	39.0	36.0	39.7	36.7	25.0	100 ± 15	100 ± 15
20	9.3	45.8	42.8	36.5	33.5	37.8	34.8	25.0	100 ± 15	100 ± 15

25	10.4	44.3	41.3	33.9	30.9	35.8	32.8	24.3	100 ± 15	100 ± 15
31.25	11.7	42.9	39.9	31.2	28.2	33.9	30.9	23.6	100 ± 15	100 ± 15
62.5	17.0	38.4	35.4	21.4	18.4	27.9	24.9	21.5	100 ± 15	100 ± 15
100	22.0	35.3	32.3	13.3	10.3	23.8	20.8	20.1	100 ± 15	100 ± 15
155	28.1	32.4	29.4	4.4	1.4	20.0	17.0	18.8		
200	32.4	30.8	27.8	4.0	1.0	17.8	14.8	18.0		

Voltage

UL Voltage Rating
300 V (CMP)

Mechanical Characteristics

Temperature

UL Temperature	Operating	Installation	Storage
75°C	-20°C To +75°C	0°C To +50°C	-20°C To +75°C

Bend Radius

Stationary Min.	Installation Min.
1.0 in (25 mm)	2.0 in (51 mm)

Max. Pull Tension:	25 lbs (11 kg)
Bulk Cable Weight:	21 lbs/1000ft (31 kg/km)

Standards and Compliance

Environmental Suitability:	Plenum, Indoor
Sustainability:	Product Lens™, Environmental Product Declaration (EPD) Available
Flammability / Reaction to Fire:	NFPA 262, UL 910 (Plenum), FT6, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca; CPR UKCA Class: Eca
NEC / UL Compliance:	Article 800, CMP
CEC / C(UL) Compliance:	CMP
ICEA Compliance:	S-90-661
IEEE Compliance:	IEEE 802.3bt Type 1, Type 2, Type 3
NEMA Compliance:	NEMA WC-63.1
Data Category:	Category 5e
TIA/EIA Compliance:	ANSI/TIA-568.2-D Category 5e
Third Party Performance Verification:	Category 5e
ISO/IEC Compliance:	ISO/IEC 11801-1, IEC 61156-5
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE), REACH: 2020-01-16
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Product Notes

Notes:	Electrical values are expected performance based on cable testing and representative performance within a typical Belden system. Values above 100 MHz are for Engineering Information Only. Print Includes Descending Footage Markings from Max. Put-Up Length to 0.
--------	--

History

Update and Revision:	Revision Number: 0.5 Revision Date: 07-14-2026
----------------------	--

Part Numbers

Variants

Item #	Color	Length	UPC
M57546B	Blue, Light	1,000 ft	799936110357
M57545B	Gray	1,000 ft	799936110333
M57924B	Orange	1,000 ft	799936110777
M57548B	Pink	1,000 ft	799936110401
M57761B	Violet	1,000 ft	799936110692
M57547B	White	1,000 ft	612825435280
M57550B	Yellow	1,000 ft	799936110425

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.