



**Product:** [6439C8](#)

Surveillance CATV MATV, RG-59 #20 BC, Duofoil® + 90% AL Braid, CMP-CATVP

Product Description

Surveillance, CATV & MATV Cable, RG59, Plenum-CMP & CATVP, 20 AWG solid bare copper, foam FEP core, Duofoil® + 90% aluminum braid, Flamarrest® jacket

Technical Specifications

Product Overview

Suitable Applications:	CATV, MATV
------------------------	------------

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Coax
20	Solid	BC - Bare Copper	0.032 in	1

Insulation

Material	Nominal Diameter
FEP - Fluorinated Ethylene Propylene (Foam)	0.133 in

Outer Shield

Type	Layer	Material	Material Trade Name	Coverage [%]
Tape	1	Tri-Laminate (Alum+Poly+Alum)	Duofoil®	100%
Braid	2	Aluminum		90%

Outer Jacket

Material	Material Trade Name	Nominal Diameter
PVC - Polyvinyl Chloride	Flamarrest®	0.199 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Conductor DCR Conductor Resistance	Nominal Outer Shield DCR	Outer Conductor DCR
10 Ohm/1000ft	10 Ohm/1000ft	5.5 Ohm/1000ft	5.5 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Shield
16.3 pF/ft

Inductance

Nominal Inductance
0.097 µH/ft

Impedance

Nominal Characteristic Impedance
75 Ohm

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
1 MHz	0.4 dB/100ft
10 MHz	0.8 dB/100ft
50 MHz	1.8 dB/100ft
100 MHz	2.6 dB/100ft
200 MHz	3.8 dB/100ft
400 MHz	5.6 dB/100ft
700 MHz	7.6 dB/100ft
900 MHz	8.8 dB/100ft
1000 MHz	9.4 dB/100ft

#### Delay

Max. Delay Skew	Nominal Delay	Nominal Velocity of Propagation (VP) [%]
83 ns/100m	1.21 ns/ft	84%

#### Voltage

UL Voltage Rating
300 V RMS

### Temperature Range

UL Temp Rating:	75°C
Operating Temperature Range:	0°C To +75°C

### Mechanical Characteristics

Bulk Cable Weight:	20 lbs/1000ft
Max. Pull Tension:	53 lbs
Min. Bend Radius/Minor Axis:	2 in

### Standards

NEC/(UL) Compliance:	CATV, CMP
CEC/C(UL) Compliance:	CMP
RG Type:	59
Series Type:	59

### Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	Yes
MII Order #39 (China RoHS):	Yes

### Suitability

Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes

### Flammability, LS0H, Toxicity Testing

UL Flammability:	NFPA 262
UL voltage rating:	300 V RMS

### Plenum/Non-Plenum

Plenum (Y/N):	Yes
---------------	-----

### Related Part Numbers

#### Variants

Item #	Color	Put-Up Type	Length	UPC
6439C8 8771000	Natural	Reel	1,000 ft	612825176862

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

Product Notes

Notes:	Print legend includes sequential footage marks.
--------	---

History

Update and Revision:	Revision Number: 0.352 Revision Date: 04-29-2024
----------------------	--

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.