



**Product:** [6662UG](#)

Nurse Call & Paging, #24-3pr, BC, Unshielded, CMP

**Product Description**

Nurse Call & Paging Cable, Plenum-CMP, 3-24 AWG solid bare copper pairs with FEP insulation, Flamarrest® jacket with ripcord

**Technical Specifications**

**Product Overview**

Suitable Applications:	Nurse Call, Commercial Sound, Annunicators, Voice Systems, Paging
------------------------	---

**Physical Characteristics (Overall)**

**Conductor**

AWG	Stranding	Material	No. of Pairs
24	Solid	BC - Bare Copper	3

Conductor Count:	6
------------------	---

**Insulation**

Material	Nominal Wall Thickness
FEP - Fluorinated Ethylene Propylene	0.007 in

**Color Chart**

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green

**Outer Shield Material**

Material
No Shield

**Outer Jacket Material**

Material	Material Trade Name	Nominal Diameter	Ripcord
PVC - Polyvinyl Chloride	Flamarrest®	0.165 in	Yes

**Electrical Characteristics**

**Conductor DCR**

Max. Conductor DCR	Max. DCR Unbalance
9.38 Ohm/1000ft	5 %

**Capacitance**

Max. Capacitance Unbalance	Nom. Mutual Capacitance
330 pF/100m	15 pF/ft

**Delay**

Frequency [MHz]	Max. Delay	Max. Delay Skew
100 MHz	538 ns/100m	45 ns/100m

## High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Min. SRL (Structural Return Loss)	Max./Min. Fitted Impedance
1 MHz	2 dB/100m	65.3 dB	62.3 dB	63.8 dB	60.8 dB	20 dB	23 dB	100 ± 15 Ohm
4 MHz	4.1 dB/100m	56.3 dB	53.3 dB	51.8 dB	48.8 dB	23 dB	23 dB	100 ± 15 Ohm
8 MHz	5.8 dB/100m	51.8 dB	48.8 dB	45.7 dB	42.7 dB	24.5 dB	23 dB	100 ± 15 Ohm
10 MHz	6.5 dB/100m	50.3 dB	47.3 dB	43.8 dB	40.8 dB	25 dB	23 dB	100 ± 15 Ohm
16 MHz	8.2 dB/100m	47.3 dB	44.3 dB	39.7 dB	36.7 dB	25 dB	23 dB	100 ± 15 Ohm
20 MHz	9.3 dB/100m	45.8 dB	42.8 dB	37.8 dB	34.7 dB	25 dB	23 dB	100 ± 15 Ohm
25 MHz	10.4 dB/100m	44.3 dB	41.3 dB	35.8 dB	32.8 dB	24.3 dB	22 dB	100 ± 15 Ohm
31.25 MHz	11.7 dB/100m	42.9 dB	39.9 dB	33.9 dB	30.9 dB	23.6 dB	21.1 dB	100 ± 15 Ohm
62.5 MHz	17 dB/100m	38.4 dB	35.4 dB	27.8 dB	24.8 dB	21.5 dB	20.9 dB	100 ± 15 Ohm
100 MHz	22 dB/100m	35.3 dB	32.3 dB	23.8 dB	20.8 dB	20.1 dB	16 dB	100 ± 15 Ohm
155 MHz	28.1 dB/100m	32.5 dB	29.5 dB	19.9 dB	16.9 dB	15.8 dB		
200 MHz	32.4 dB/100m	30.8 dB	27.8 dB	17.7 dB	14.7 dB	15 dB		

## Voltage

<b>UL Voltage Rating</b>
300 V RMS

## Temperature Range

Operating Temp Range:	-5°C To +75°C
-----------------------	---------------

## Mechanical Characteristics

Bulk Cable Weight:	15.75 lbs/1000ft
Max. Pull Tension:	26 lbs
Min Bend Radius/Minor Axis:	1.75 in

## Standards

CEC/C(UL) Compliance:	CMP
TIA/EIA Compliance:	568-B.2 Category 5e
Other Compliance:	NEMA WC-63.1 Category 5e, UL Verified to Category 5e

## Applicable Environmental and Other Programs

Environmental Space:	Plenum
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
MII Order #39 (China RoHS):	Yes

## Suitability

Suitability - Indoor:	Yes
-----------------------	-----

## Flammability, LS0H, Toxicity Testing

UL Flammability:	NFPA 262
UL voltage rating:	300 V RMS

## Plenum/Non-Plenum

Plenum (Y/N):	Yes
---------------	-----

## Part Number

Non-Plenum Number:	5662UG
--------------------	--------

## Variants

Item #	Color	Putup Type	Length	UPC
6662UG F6H1000	Gray, Dark Pearl	Reel	1,000 ft	612825179016

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

## Product Notes

Notes:	Electrical values are expected performance based on cable testing and representative performance within a typical Belden system. Jacket sequentially marked at 2 ft. intervals. Third party verified to TIA/EIA-568-B.2, Category 5e.
--------	---

## History

Update and Revision:	Revision Number: 0.147 Revision Date: 04-03-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.