



Part Number: 6663U6

CAT6 Horizontal Security, 4pr, UTP, LS-PVC Jkt, CMP

Product Description

Surveillance Category 6 Cable, Plenum-CMP, 4-23 AWG solid bare copper pairs with FEP insulation, UTP, Flamarrest® jacket with ripcord

Technical Specifications

Product Overview

Environmental Space:	Plenum
Suitable Applications:	Video, Sound & Security, Premise Horizontal Cable, Gigabit Ethernet, 100BaseTX, 100BaseVG ANYLAN, 155 ATM, 622 ATM, 250MHz CAT6

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
23	Solid	BC - Bare Copper	4

Conductor Count:	8
Total Number of Pairs:	4

Insulation

Material
FRPO/FEP - Flame Retardant Polyolefin/Fluorinated Ethylene Propylene

Bonded-Pair:	N/A
--------------	-----

Color Chart

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

Outer Jacket Material

Material	Material Trade Name	Nominal Diameter	Ripcord
LS PVC - Low Smoke Polyvinyl Chloride	Flamarrest®	0.225 in	Yes

Electrical Characteristics

Conductor DCR

Max. Conductor DCR	Max. DCR Unbalance
93.8 Ohm/km	5 %

Capacitance

Max. Capacitance Unbalance	Nom. Mutual Capacitance
330 pF/ft	15 pF/ft

Delay

Frequency [MHz]	Max. Delay	Max. Delay Skew	Nominal Velocity of Propagation (VP) [%]
100 MHz	537 ns/100m	45 ns/100m	72 %

High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted)	Max./Min. Fitted Impedance	Min. TCL [dB]	Min. ELTCTL [dB]
1 MHz	2 dB/100m	74.3 dB	72.3 dB	72.3 dB	70.3 dB	67.8 dB	64.8 dB	20 dB	100 ± 15	100 ± 15	40.0 dB	35.0 dB
4 MHz	3.8 dB/100m	65.3 dB	63.3 dB	61.5 dB	59.5 dB	55.8 dB	52.7 dB	23 dB	100 ± 15	100 ± 15	40.0 dB	23.0 dB
8 MHz	5.3 dB/100m	60.8 dB	58.8 dB	55.4 dB	53.4 dB	49.7 dB	46.7 dB	24.5 dB	100 ± 15	100 ± 15	40.0 dB	16.9 dB
10 MHz	6 dB/100m	59.3 dB	57.3 dB	53.3 dB	51.3 dB	47.8 dB	44.8 dB	25 dB	100 ± 15	100 ± 15	40.0 dB	15.0 dB
16 MHz	7.6 dB/100m	56.2 dB	54.3 dB	48.7 dB	46.7 dB	43.7 dB	40.7 dB	25 dB	100 ± 15	100 ± 15	38.0 dB	10.9 dB
20 MHz	8.5 dB/100m	54.8 dB	52.8 dB	46.3 dB	44.3 dB	41.8 dB	38.8 dB	25 dB	100 ± 15	100 ± 15	37.0 dB	9.0 dB
25 MHz	9.5 dB/100m	53.3 dB	51.3 dB	43.8 dB	41.8 dB	39.8 dB	36.8 dB	24.3 dB	100 ± 15	100 ± 15	36.0 dB	7.0 dB
31.25 MHz	10.7 dB/100m	51.9 dB	49.9 dB	41.2 dB	39.2 dB	37.9 dB	34.9 dB	23.6 dB	100 ± 15	100 ± 15	35.1 dB	5.1 dB
62.5 MHz	15.4 dB/100m	47.4 dB	45.4 dB	32 dB	30 dB	31.9 dB	28.9 dB	21.5 dB	100 ± 15	100 ± 15	32.0 dB	
100 MHz	19.8 dB/100m	44.3 dB	42.3 dB	24.5 dB	22.5 dB	27.8 dB	24.8 dB	20.1 dB	100 ± 15	100 ± 15	30.0 dB	
155 MHz	25.2 dB/100m	41.5 dB	39.5 dB	16.3 dB	14.3 dB	23.9 dB	20.9 dB	18.8 dB	100 ± 20	100 ± 15	28.1 dB	
200 MHz	29 dB/100m	39.8 dB	37.8 dB	10.8 dB	8.8 dB	21.8 dB	18.8 dB	18 dB	100 ± 20	100 ± 15	27.0 dB	
250 MHz	32.8 dB/100m	38.3 dB	36.3 dB	5.5 dB	3.5 dB	19.8 dB	16.8 dB	17.3 dB	100 ± 20	100 ± 15	26.0 dB	

Segregation class according EN50174-2:

a

Voltage

UL Voltage Rating

300 V RMS

Temperature Range

Installation Temp Range:	0°C To +60°C
UL Temp Rating:	75°C
Storage Temp Range:	-20°C To +60°C
Operating Temp Range:	-20°C To +75°C

Mechanical Characteristics

Bulk Cable Weight:	28 lbs/1000ft
Max Recommended Pulling Tension:	40 lbs
Min Bend Radius During Installation:	2.25 in
Min Bend Radius/Minor Axis:	0.9 in

Standards

NEC/(UL) Specification:	CMP
CEC/C(UL) Specification:	CMP
ISO/IEC Compliance:	11801 ed 2.2 (2011) Class E
CPR Euroclass:	Eca
Data Category:	Category 6
ANSI Compliance:	S-116-732-2013 Category 6, ANSI/NEMA WC-66 Category 6
Telecommunications Standards:	Category 6 - TIA 568.C.2
IEEE Specification:	IEEE 802.3bt Type 1, Type 2, Type 3, Type 4
Other Specification:	Third party Verified to Category 6
Third Party Performance Verification:	Category 6

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	Yes
EU CE Mark:	Yes
EU REACH SVHC Compliance (yyyy-mm-dd):	2017-07-10
EU RoHS Compliance Date (yyyy-mm-dd):	2009-03-12

CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Aerial:	No
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Non-Halogenated:	No
Suitability - Oil Resistance:	No
Suitability - Outdoor:	No
Suitability - Sunlight Resistance:	No

Flammability, LS0H, Toxicity Testing

UL Flammability:	NFPA 262 Plenum Flame Test (UL910)(FT6)
CSA Flammability:	FT6
ISO/IEC Flammability:	IEC 60332-1-2
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	Yes
---------------	-----

Part Number

Non-Plenum Number:	5663U6
--------------------	--------

Variants

Item #	Color	UPC	Footnote
6663U6 0101000	Black	612825178866	C
6663U6 010500	Black	612825178873	

Footnote:	C - CRATE REEL PUT-UP.
Patent:	https://www.belden.com/resources/patents

Product Notes

Notes:	Jacket sequentially marked at 2 ft. intervals. Third party verified to ANSI/TIA-568-C.2, Category 6.
--------	--

History

Update and Revision:	Revision Number: 0.344 Revision Date: 08-22-2019
----------------------	--

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.