



Product: [62P1604](#)

Inst PVC/PVC, 4 Pr #16 Str BC, PVC-NYL Ins E1, IS/OS, Blk PVC Jkt, TC-ER NPLF 90C Dry 75C Wet

Product Description

UL Instrumentation, 4 Pair 16AWG (7x24) Bare Copper, PVC-NYL Insulation E1 Color Code, Individual & Overall Beldfoil® Shield, Black PVC Outer Jacket, TC-ER NPLF 90C Dry 75C Wet SUN RES DIR BUR

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
16	7x24	BC - Bare Copper	4

Conductor Count: 8

Insulation

Material	Nominal Diameter
PVC/Nylon - Polyvinyl Chloride + Nylon	0.101 in

Color Chart

Number	Color
Pair	ICEA S-73-732 Table E1 (Pairs: Black & White and numbered)

Inner Shield Material

Type	Material	Material Trade Name	Drainwire Material	Drainwire Diameter	Drainwire AWG
Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	TC - Tinned Copper	0.0363 in	20

Outer Shield Material

Type	Material	Material Trade Name
Tape	Bi-Laminate (Alum+Poly)	Beldfoil®

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness	Separator Material
PVC - Polyvinyl Chloride	0.585 in	0.063 in	Barrier Tape

Electrical Characteristics

Current

Max. Recommended Current [A]
12.6 Amps per Conductor at 30°C

Voltage

UL Voltage Rating
150 V RMS (Type NPLF)

Mechanical Characteristics

Max. Pull Tension:	348 lbs
Min Bend Radius/Minor Axis:	7 in

Standards

NEC/(UL) Compliance:	TC-ER
IEEE Compliance:	1202

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes

Suitability

Suitability - Burial:	Yes
Suitability - Sunlight Resistance:	Yes

Flammability, LS0H, Toxicity Testing

C(UL) Flammability:	FT4
IEEE Flammability:	1202
UL voltage rating:	600 V RMS (Type TC)

Part Number

Variants

Item #	Putup Type	UPC
62P1604 0105000	Reel	612825359791
62P160401010000	Reel	612825359760

History

Update and Revision:	Revision Number: 0.32 Revision Date: 02-16-2021
----------------------	---

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.