



Product: [70045LV](#)

SPEAKERCABLE LSZH 2x1.5mm²

Product Description

SPEAKERCABLE LSZH 2x1.5mm²

Technical Specifications

Product Overview

Suitable Applications:	Speaker cable for use in indoor or outdoor applications
------------------------	---

Physical Characteristics (Overall)

Conductor

Stranding	Material	Cross Section	Construction n x D
Stranded	BC-OFHC - Oxygen-Free Bare Copper (High Conductivity)	1.50 mm ²	30x0.25 mm

Conductor Count:	2
------------------	---

Insulation

Type	Material	Nominal Diameter	Diameter +/- Tolerance
Insulation	LSZH - Low Smoke Zero Halogen (Flame Retardant)	2.30 mm	0.07 mm

Color Chart

Number	Color
Wire 1	Black
Wire 2	Red

Outer Jacket Material

Material	Nominal Diameter	Diameter +/- Tolerance
LSZH - Low Smoke Zero Halogen (Flame Retardant)	6.80 mm	0.25 mm

Table Notes:	Flexible with Matte Finish
--------------	----------------------------

Construction and Dimensions

Cabling

Description
2 wires twisted

Electrical Characteristics

Conductor DCR

Max. Conductor DCR
13 Ohm/km

Voltage

Voltage Rating [V]
300 V

Temperature Range

Storage Temp Range:	-30°C to +70°C
Operating Temp Range (Flexible Install):	-5°C To +60°C
Operating Temp Range (Fixed Install):	-30°C To +70°C

Mechanical Characteristics

Max. Pull Tension:	200 N
--------------------	-------

Standards

CPR Euroclass:	B2ca-s1,d1,a1
----------------	---------------

Applicable Environmental and Other Programs

Environmental Space:	Indoor/Outdoor - Euroclass B2ca
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01

Flammability, LSOH, Toxicity Testing

IEC Flammability:	IEC 60332-1-2
IEC 60754-1 (EN50267-1)- Halogen Amount:	Zero
IEC 60754-2 (EN50267-2)- Halogen Acid Gas Amount - Max. Conductivity:	2.5 µS/mm
IEC 60754-2 (EN50267-2)- Halogen Acid Gas Amount - Min. pH:	4.3

Part Number

Variants

Item #	Color	Putup Type	Length	EAN
70045LV.00100	Black	Reel	100 m	8719605163370
70045LV.00250	Black	Reel	250 m	8719605163387
70045LV.00500	Black	Reel	500 m	8719605163363
70045LV.01100	Gray	Reel	100 m	8719605177643
70045LV.01250	Gray	Reel	250 m	8719605177650

History

Update and Revision:	Revision Number: 0.35 Revision Date: 06-24-2020
----------------------	---

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.