



Product: [6302UE](#)

Security & Sound, #18-4c, BC, CMP

Product Description

Security & Sound Cable, Plenum-CMP 4-18 AWG stranded bare copper conductors with Flamarrest® insulation, Flamarrest® jacket with ripcord

Technical Specifications

Product Overview

Suitable Applications:	Security System, Intercom/PA, Audio/Speaker, Power-Limited Controls
------------------------	---

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	4	18	7x26	BC - Bare Copper

Insulation

Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
PVC - Polyvinyl Chloride	0.009 in (0.23 mm)	0.047 in (1.2 mm)	Black, Red, White, Green

Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.015 in (0.38 mm)	0.18 in (4.6 mm)	Yes

Electrical Characteristics

Electricals

Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Max. Current
6.79 Ohm/1000ft	34 pF/ft (110 pF/m)	4 Amps per Conductor at 25°C (10°C Temperature Rise)

Voltage

UL Voltage Rating
300 V

Mechanical Characteristics

Temperature

UL Temperature	Operating	Installation
75°C	-10°C To +75°C	0°C To +75°C

Bend Radius

Stationary Min.	Installation Min.
1.8 in (46 mm)	1.8 in (46 mm)

Max. Pull Tension:	83.2 lbs (37.7 kg)
Bulk Cable Weight:	30 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor, Outdoor
----------------------------	-----------------

Flammability / Reaction to Fire:	NFPA 262 (UL910), FT6, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 800, CMP
CEC / C(UL) Compliance:	CMP
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Non-Plenum Number:	5302UE

History

Update and Revision:	Revision Number: 0.437 Revision Date: 02-03-2025
----------------------	--

Part Numbers

Variants

Item #	Color	UPC	Footnote
6302UE 8771000	Natural	612825340232	C
6302UE 877500	Natural	612825175391	
6302UE 877C250	Natural		
6302UE 877U1000	Natural	612825175377	
6302UE 877U500	Natural	612825175384	

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.