




**Product:** [734A1P](#) 

DS3/DS4 Central Office Coax, RG-59, 20 AWG Solid BC, Foil + 85% TC Braid, Flamarrest® Jkt, CMP

### Product Description

DS3/DS4 Central Office Coax, RG-59, 20 AWG Solid Bare Copper Conductor, FEP Insulation, Foil + 85% Tinned Copper Braid Shield, Flamarrest® Jacket, CMP

### Technical Specifications

#### Product Overview

Suitable Applications:	Central office wiring, DS3/DS4 interconnect, 734/735 telecommunications systems, switchboard communications
------------------------	---

#### Construction Details

RG Type:	59
----------	----

#### Conductor

AWG	Stranding	Nom. Diameter	Material
20	Solid	0.032 in	BC - Bare Copper

#### Insulation

Material	Nom. Diameter
FEP - Fluorinated Ethylene Propylene (Foam)	0.148 in

#### Outer Shield Material

Layer	Outer Shield Type	Material	Material Trade Name	Coverage
1	Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	100%
2	Braid	Tinned Copper (TC)		85%

#### Outer Jacket Material

Material	Nom. Diameter
PVC - Polyvinyl Chloride	0.213 in

#### Electrical Characteristics

##### Return Loss (RL)

Frequency [MHz]	Min. Return Loss [dB]
15 - 95 MHz	30 dB

##### Electricals

Nom. Conductor DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Impedance	Nom. Velocity
10.1 Ohm/1000ft	2.4 Ohm/1000ft	17.3 pF/ft	75 Ohm	80%

##### Voltage

UL Voltage Rating
300 V (CMP)

#### Mechanical Characteristics

##### Temperature

UL Rating	Operating

60°C 0°C to +75°C

#### Bend Radius

##### Installation Min.

2.1 in

Bulk Cable Weight: 35 lbs/1000ft

Max. Pull Tension: 49 lbs

#### Standards and Compliance

Environmental Suitability: Indoor - Plenum, Indoor

Sustainability: CA Prop 65

Flammability / Fire Resistance: NFPA 262

NEC / UL Compliance: CMP

CEC / C(UL) Compliance: CMP

European Directive Compliance: EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)

APAC Compliance: China RoHS II (GB/T 26572-2011)

Non-Plenum Number: 734A1

#### History

Update and Revision: Revision Number: 0.319 Revision Date: 05-26-2021

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.