



**Product:** [735A3](#) 



DS-3 and DS-4, 735\* Series, #26-3 SPC Coax, CMR/CMG

**Product Description**

26 AWG solid .016" silver-plated copper conductor(s), foam HDPE insulation, Beldfoil®; tinned copper braid shield (95% coverage), PVC jacket.

**Technical Specifications**

**Physical Characteristics (Overall)**

**Conductor**

AWG	Stranding	Material	Nominal Diameter	No. of Coax
26	Solid	SCCS - Silvered Copper Covered Steel	0.016 in	3

Conductor Count:	3
------------------	---

**Insulation**

Material	Nominal Diameter
PE - Polyethylene (Foam)	0.077 in

**Inner Shield Material**

Type	Layer	Material	Material Trade Name	Coverage [%]
Tape	1	Bi-Laminate (Alum+Poly)	Beldfoil®	100%
Braid	2	Tinned Copper (TC)		95%

**Inner Jacket Material**

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.129 in

**Outer Shield Material**

Material
No Shield

**Outer Jacket Material**

Material	Nominal Diameter	Ripcord
PVC - Polyvinyl Chloride	0.320 in	Yes

**Electrical Characteristics**

**Conductor DCR**

Nominal Conductor DCR	Nominal Conductor DCR	Conductor Resistance	Nominal Outer Shield DCR	Outer Conductor DCR
41 Ohm/1000ft	41 Ohm/1000ft		5.3 Ohm/1000ft	5.3 Ohm/1000ft

**Capacitance**

Nom. Capacitance Conductor to Shield
17.7 pF/ft

**Inductance**

Nominal Inductance
0.19 µH/ft

## Impedance

### Nominal Characteristic Impedance

75 Ohm

## Return Loss (RL)

### Frequency [MHz] | Minimum Return (RL)

15-95 MHz | 30 dB

## Delay

### Nominal Delay | Nominal Velocity of Propagation (VP) [%]

1.34 ns/ft | 76%

## High Freq

### Frequency [MHz] | Max. Insertion Loss (Attenuation)

1 MHz	0.6 dB/100ft
1.024 MHz	0.61 dB/100ft
4.224 MHz	1.1 dB/100ft
5 MHz	1.2 dB/100ft
10 MHz	1.7 dB/100ft
17.184 MHz	2.2 dB/100ft
22.368 MHz	2.5 dB/100ft
25.92 MHz	2.7 dB/100ft
44.736 MHz	3.6 dB/100ft
50 MHz	3.8 dB/100ft
69.632 MHz	4.5 dB/100ft
77.76 MHz	4.8 dB/100ft
100 MHz	5.5 dB/100ft
137.088 MHz	6.4 dB/100ft
200 MHz	7.8 dB/100ft

## Voltage

### UL Voltage Rating

300 V RMS

## Temperature Range

Operating Temp Range: -40°C To +75°C

## Mechanical Characteristics

Bulk Cable Weight:	49 lbs/1000ft
Max. Pull Tension:	75 lbs
Min Bend Radius (Overall):	3.25 in
Min Bend Radius (Each Coax):	1.25 in

## Standards

NEC/(UL) Compliance:	CMR
CEC/C(UL) Compliance:	CMG
RG Type:	Mini 59
Other Compliance:	Telcordia Specification GR-139-Core

## Applicable Environmental and Other Programs

Environmental Space:	Indoor - Riser
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
MII Order #39 (China RoHS):	Yes

## Suitability

Suitability - Indoor:	Yes
-----------------------	-----

## Flammability, LSOH, Toxicity Testing

UL Flammability:	UL1666 Vertical Shaft
CSA Flammability:	FT4
UL voltage rating:	300 V RMS

## Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

## Part Number

### Variants

Item #	Color	Putup Type	Length	UPC
735A3 008500	Gray	Reel	500 ft	612825184812
735A3 0081000	Gray	Reel	1,000 ft	612825184805

## History

Update and Revision:	Revision Number: 0.163 Revision Date: 09-30-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.