



**Product:** [73604W](#)

MachFlex™, 4 C #16 Str BC, PVC Ins, PVC Jkt, AWM 2587 CLASS K

[Request Sample](#)

**Product Description**

MachFlex™ for Moderate Flex, 4 Conductor 16AWG (26x30) Bare Copper, PVC Insulation, PVC Outer Jacket, AWM 2587 CLASS K

**Technical Specifications**

**Physical Characteristics (Overall)**

**Conductor**

AWG	Stranding	Material	No. of Conductors
16	26x30	BC - Bare Copper	3
16		BC - Bare Copper	1

Conductor Count: 4

**Insulation**

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.104 in	0.022 in
PVC - Polyvinyl Chloride		

**Color Chart**

Color
Black and Numbered

**Outer Shield Material**

Type	Material
No Shield	No Shield

**Outer Jacket Material**

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.328 in	0.035 in

**Electrical Characteristics**

**Conductor DCR**

Nominal Conductor DCR
4.1 Ohm/1000ft

**Capacitance**

Nom. Capacitance Conductor to Conductor
34 pF/ft

**Inductance**

Nominal Inductance
.180 µH/ft

**Voltage**

UL Voltage Rating
600 V

## Temperature Range

UL Temp Rating:	90°C
Operating Temp Range:	-40°C To 90°C (Static), -5°C To 90°C (Flexing)

## Mechanical Characteristics

Oil Resistance:	Yes
Flex Cycle Rating:	1 Million Cycles
Bulk Cable Weight:	132 lbs/1000ft
Max. Pull Tension:	82 lbs
Min Bend Radius (Continuous Flexing):	1.6 in
Min Bend Radius/Minor Axis:	1.6 in

## Standards

UL AWM Style Compliance:	AWM 2587
CSA AWM Compliance:	AWM I/II A/B
Other Compliance:	VDE 0472, Section 803 Oil Test

## Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes

## Flammability, LSOH, Toxicity Testing

CSA Flammability:	FT1
UL voltage rating:	600 V RMS

## Part Number

### Variants

Item #	Color	Putup Type	UPC
73604W 008100	Gray	Reel	612825409762
73604W 0081000	Gray	Reel	612825409779
73604W 008500	Gray	Reel	612825409786

## History

Update and Revision:	Revision Number: 0.57 Revision Date: 02-16-2021
----------------------	---

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.