



Product: [6504FE](#)

Security & Sound, #22-6c BC, Shielded, CMP

### Product Description

Security & Sound Cable, Plenum-CMP, 6-22 AWG stranded bare copper conductors with Flamarrest® insulation, Beldfoil® shield and Flamarrest® jacket with ripcord

### Technical Specifications

#### Product Overview

Suitable Applications:	Security System, Intercom/PA, Audio/Speaker, Power-Limited Controls, Noisy Environment
------------------------	--

#### Construction Details

##### Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	6	22 AWG	7x30	BC - Bare Copper

##### Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PVC - Polyvinyl Chloride	0.009 in (0.23 mm)	0.047 in (1.2 mm)	Black, Red, White, Green, Brown, Blue

##### Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	24 AWG (7x32) TC

##### Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.015 in (0.38 mm)	0.175 in (4.45 mm)	Yes

Overall Cable Diameter (Nominal): 0.175 in (4.45 mm)

#### Electrical Characteristics

##### Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Max. Current
Conductor(s)	16.2 Ohm/1000ft	33 pF/ft (110 pF/m)	59 pF/ft (190 pF/m)	1.9 Amps per Conductor at 25°C

##### Voltage

###### UL Voltage Rating

300 V (CMP)

#### Mechanical Characteristics

##### Temperature

UL Temperature	Operating
75°C	0°C to +75°C

##### Bend Radius

Stationary Min.	Installation Min.
1.75 in (44.5 mm)	1.75 in (44.5 mm)

Max. Pull Tension:	60 lbs (27 kg)
Bulk Cable Weight:	24 lbs/1000ft

## Standards and Compliance

Environmental Suitability:	Indoor - Plenum, Indoor
Flammability / Reaction to Fire:	NFPA 262, UL 910 (Plenum), FT6
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 800, CMP
CEC / C(UL) Compliance:	CMP
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Non-Plenum Number:	5504FE

## History

Update and Revision:	Revision Number: 0.438 Revision Date: 04-03-2023
----------------------	--

## Part Numbers

### Variants

Item #	Color	Putup Type	Length	UPC	Footnote
6504FE 877U250	Natural	UnReel	250 ft	612825177852	
6504FE 877500	Natural	Reel	500 ft	612825177883	C
6504FE 877C500	Natural	Coil	500 ft	612825177838	
6504FE 877U500	Natural	UnReel	500 ft	612825177869	
6504FE 877Z500	Natural	ReelTuff Box	500 ft		
6504FE 8771000	Natural	Reel	1,000 ft	612825177876	C
6504FE 877U1000	Natural	UnReel	1,000 ft	612825177845	
6504FE 877Z1000	Natural	ReelTuff Box	1,000 ft	612825423829	
6504FE 0031000	Orange	Reel	1,000 ft	612825350729	
6504FE 003U1000	Orange	UnReel	1,000 ft	612825350736	
6504FE 003Z1000	Orange	ReelTuff Box	1,000 ft	612825423805	
6504FE 0071000	Violet	Reel	1,000 ft	612825177821	
6504FE 0041000	Yellow	Reel	1,000 ft	612825177814	
6504FE 004U1000	Yellow	UnReel	1,000 ft	612825177807	
6504FE 004Z1000	Yellow	ReelTuff Box	1,000 ft	612825423812	

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.