



**Product:** [6508FE](#)

Security & Sound, #22-10c BC, Shielded, CMP

## Product Description

Security & Sound Cable, Plenum-CMP, 10-22 AWG stranded bare copper conductors with Flammarrest® insulation, Beldfoil® shield and Flammarrest® jacket with ripcord

## Technical Specifications

### Product Overview

Suitable Applications:	Security System, Intercom/PA, Audio/Speaker, Power-Limited Controls, Noisy Environment
------------------------	--

### Construction Details

#### Conductor

Element	Number of Element	AWG	Stranding	Material
Conductor(s)	10	22	7x30	BC - Bare Copper

#### Insulation

Element	Material	Thickness	Color Code
Conductor(s)	PVC - Polyvinyl Chloride	0.009 in	Black, Red, White, Green, Brown, Blue, Orange, Yellow, Purple, Gray

#### Outer Shield Material

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	24 AWG (7x32) TC

#### Outer Jacket Material

Material	Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.015 in	0.222 in	Yes

Cable Diameter (Nominal):	0.222 in
---------------------------	----------

### Electrical Characteristics

#### Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Max. Current
Conductor(s)	16.2 Ohm/1000ft	33 pF/ft	59 pF/ft	2 Amps per conductor @ 25°C
Nom Outer Shield DCR:	13.9 Ohm/1000ft			

#### Voltage

UL Voltage Rating
300 V (CMP)

### Mechanical Characteristics

#### Temperature

UL Rating	Operating
75°C	0°C to +75°C

#### Bend Radius

Stationary Min.	Installation Min.
2.25 in	2.2 in

Max. Pull Tension:	97 lbs
Bulk Cable Weight:	38 lbs/1000ft

## Standards and Compliance

Environmental Suitability:	Indoor - Plenum, Indoor
Flammability / Fire Resistance:	NFPA 262, UL 910 (Plenum), FT6, IEC 60332-1-2
NEC / UL Compliance:	Article 800, CMP
CEC / C(UL) Compliance:	CMP
CPR Euroclass:	Eca
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (ROHS II), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Non-Plenum Number:	5508FE

## History

Update and Revision:	Revision Number: 0.278 Revision Date: 09-30-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.