



Product: [74005NH](#)

DataTuff® 7, 4PR #26 Str BC, PO ins, S/FTP, LSNH Jkt, AWM 20851

Product Description

DataTuff® 7, 4 Pair AWG 26 Bare Copper - Stranded, Polyethylene insulation, S/FTP - Overall Braid / Individual Foil shielding, LSZH / FRNC jacket , AWM 20851

Technical Specifications

Product Overview

Suitable Applications:	Cat7, harsh environment, IIoT, factory or process automation, video, audio, data communication, etc.
------------------------	--

Construction Details

Conductor

Size	Stranding	Material	No. of Pairs	No. of Elements
26 AWG	7x0.16 mm	BC - Bare Copper	4	8

Insulation

Material	Nom. Insulation Diameter	Color Code
PE - Polyethylene (Foam)	1.05 mm (0.0413 in)	White & Blue, White & Orange, White & Green, White & Brown

Cable Core

Description
4 pairs twisted to cable core

Inner Shield

Element	Shield Type	Material
Individual Shielded Pair	Tape	Bi-Laminate (Alum+Poly)

Table Notes:	Aluminum outside
--------------	------------------

Outer Shield

Shield Type	Material	Coverage
Braid	Tinned Copper (TC)	65%

Outer Jacket

Material	Nom. Diameter
LSZH - Low Smoke Zero Halogen (Flame Retardant)	6.8 mm (0.27 in)

Overall Cable Diameter (Nominal):	6.8 mm (0.27 in)
-----------------------------------	------------------

Electrical Characteristics

Electricals

Max. Conductor DCR	Max. Mutual Capacitance	Max. Capacitance Unbalance	Nom. Characteristic Impedance
145 Ohm/km	56 pF/m (17 pF/ft)	160 pF/100m	100 Ohm

Delay

Max. Delay Skew	Nom. Velocity of Prop.
40 ns/100m	70%

High Frequency

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]
1	2.7 dB/100m	80	77			
4	5.5 dB/100m	80	77	80	77	23
10	8.5 dB/100m	80	77	74	71	25
16	10.8 dB/100m	80	77	69.9	66.9	25
20	12.1 dB/100m	80	77	68	65	25
31.25	15.2 dB/100m	80	77	64.1	61.1	23.6
62.5	21.8 dB/100m	75.1	72.1	58.1	55.1	21.5
100	27.8 dB/100m	72.4	69.4	54	51	20.1
200	40.1 dB/100m	67.9	64.9	48	45	18
300	50 dB/100m	65.3	62.3	44.5	41.5	17.3
600	73.3 dB/100m	60.8	57.8	38.4	35.4	17.3

Transfer Impedance

Frequency	Max. Transfer Impedance
10 Mhz	Max. 5 mOhm/m

Voltage

UL Voltage Rating	Voltage Rating
30 V RMS	450 V DC and 300 V AC

Mechanical Characteristics

Temperature

Operating	Installation	Storage
-40°C to +80°C	-15°C To +60°C	-40°C to +80°C

Bend Radius

Stationary Min.	Installation Min.
30 mm (1.2 in)	65 mm

Max. Pull Tension: 80 N (18 lbf)

Standards and Compliance

Environmental Suitability:	Indoor - Euroclass Dca, Sunlight Resistance, Oil Resistance
Flammability / Reaction to Fire:	IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Dca-s1,d1,a1
AWM Compliance:	AWM 20851
Data Category:	Category 7
TIA/EIA Compliance:	ANSI/TIA 568.2-D
ISO/IEC Compliance:	ISO/IEC 11801-1
CENELEC Compliance:	EN 50173-1
European Halogen Free Standards:	IEC 62821-1 Halogen Free Compliance = Yes, IEC 60754-1 - Halogen Amount = Zero, IEC 60754-2 - Halogen Acid Gas Amount - Max. Conductivity = 2.5 µS/mm, IEC 60754-2 - Halogen Acid Gas Amount - Min. pH = 4.3
European Directive Compliance:	EU CE Mark
UK Regulation Compliance:	UKCA Mark

History

Update and Revision: Revision Number: 0.269 Revision Date: 04-29-2024

Part Numbers

Variants

Item #	Color	Putup Type	Length	EAN
74005NH.07500	Black	Reel	500 m	8719605013262
74005NH.11500	Blue	Reel	500 m	8719605013309
74005NH.10500	Gray, RAL 7032	Reel	500 m	8719605013293
74005NH.08500	Green	Reel	500 m	8719605013279
74005NH.09500	Orange	Reel	500 m	8719605013286
74005NH.13500	Red	Reel	500 m	8719605013323
74005NH.14500	White	Reel	500 m	8719605204417

74005NH.12500	Yellow	Reel	500 m	8719605013316
---------------	--------	------	-------	---------------

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.